


NOTES: UNLESS OTHERWISE SPECIFIED,

1. ARTWORK P/N DC553A
2. FAB PER IPC-A-600
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE .062 +/- .005 INCH
WITH 2 OZ. COPPER ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD.
4-LAYER
SOLDERMASK OVER BARE COPPER.
WHITE TIN BOTH SIDES.
SOLDER MASK TYPE: WET PHOTO-IMAGEABLE
THE PCB COLOR: GREEN
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DROP ALL UNUSED PADS ON INNER LAYERS.
8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
9. SCORING:



Fabrication Drawing

SIZE	QTY	SYM	PLTD
125	4	+	PLTD
94	9	×	PLTD
10	7	□	PLTD
31	6	◇	PLTD
70	2	⊗	NPLTD

<div>  <div> LINEAR TECHNOLOGY </div> </div>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
APPROVALS		TITLE: LTC3450EUD	
DRAWN	INIT	DATE	Triple Output TFT-LCD Supply
CHECK			
DESIGN			
ENGR			
SCALE = NONE		SIZE NONE	REV. A
DES-230564		SH1 of 1	