





SIZE	QTY	SYM	PLATED	TOL
0.25	223	◇	YES	+/-0.08
0.51	19	⊕ ^A	YES	+/-0.08
0.76	13	⊗	YES	+/-0.08
1.78	2	×	NO	+/-0.13
2.41	20	□	YES	+/-0.13
4.75	4	+	NO	+/-0.13
5.21	2	⊠	YES	+/-0.25

NOTES: UNLESS OTHERWISE SPECIFIED,

- ARTWORK P/N DC2122A REV 2.
- FAB PER IPC-A-600
- PCB SHALL BE RoHS COMPLIANT.
- MATERIAL:
 - LAMINATE: EPOXY FIBERGLASS, NEMA GRADE FR-4 FLAMMABILITY RATING: 94 V-2 MINIMUM.
 - THICKNESS: 1.6 +/- 0.1 mm
 - CLAD: 2 OZ. (50um) EXTERNAL LAYERS.
1 OZ. (25um) COPPER ON 4 INTERNAL LAYERS.
- FINISH:
 - COATING: SOLDERMASK OVER BARE COPPER, COLOR, GREEN LPI.
 - PLATING: GOLD IMMERSION BOTH SIDES.
 - SILKSCREEN: COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.
- TOLERANCES:
 - WARPAGE: (0.075mm) MAX. ALONG THE LONGEST DIAG. AS PER IPC-TM650 METHOD 2.4.22.
 - ETCHING: +0.03mm, -0.3mm OF MASTER PATTERN.
 - REGISTRATION: 0.075mm MAX.
 - MASK THICKNESS: 0.025mm MIN., 0.075mm MAX.
 - HOLE PLATING: 22um +/- 3um.
- SIZE:
 - CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- HOLE DIAMETERS ARE POST-PLATED SIZES.
- DEBURR AND BREAK ALL SHARP EDGES.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:
 



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON ANGLE $\pm 1^\circ$		CONTRACT NO.		 1830 McCarthy Blvd. Milpitas, CA 95035 Phone: (408)432-1900 Fax: (408)434-0507	
.XX ± 0.25 .XXX ± 0.127		APPROVALS		TITLE	
THIRD ANGLE PROJECTION		DRAWN MI		DATE	
		CHECKED		06/11/13	
		DING L APPROVED		09/23/13	
DO NOT SCALE DRAWING		DESIGNED BY		SCALE 1/1	
				FILENAME: 2122A-2.PCB	
				SHEET 1 OF 1	
				DWG NO. DC2122A	
				REV 2	