



## LAYER STRUCTURE



- 



SIZE	QTY	SYM	PLATED	TOL
0.19	4	+	YES	+/-0.003
0.031	6	X	YES	+/-0.003
0.07	2	□	NO	+/-0.003
0.01	95	◇	YES	+/-0.003
0.094	4	⊗	YES	+/-0.003

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ±1° $0.XXX'' = \pm 0.01''$ $0.XXX'' = \pm 0.005''$ INTERPRET DIM AND TOL PER ASME Y14.5M-1994	APPROVALS		1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 <a href="http://WWW.MCPC.COM">WWW.MCPC.COM</a> LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	PCB DES.	NC	<b>TECHNOLOGY</b>  TITLE: FABRICATION DRAWING: 40V, 1A BUCK-BOOST DC/DC CONVERTER WITH PROGRAMMABLE OUTPUT CURRENT	
	APP ENG.	J.NOON		
THIRD ANGLE PROJECTION  			SIZE N/A	IC NO. DC3T114EDHC-1 DEMO CIRCUIT 1821B
			REV.	1
DO NOT SCALE DRAWING	SCALE: NONE		FILENAME:	DC1821B-1.PCB
			SHT 1 of 1	