



KSZ8081RNB / KSZ8091RNB

10Base-T/100Base-TX Physical Layer Transceiver

Evaluation Board User's Guide

Revision 1.0 / August 2012

© Micrel, Inc. 2012
All rights reserved

Micrel is a registered trademark of Micrel and its subsidiaries in the United States and certain other countries. All other trademarks are the property of their respective owners.

The information furnished by Micrel in this datasheet is believed to be accurate and reliable. However, no responsibility is assumed by Micrel for its use. Micrel reserves the right to change circuitry and specifications at any time without notification to the customer. Micrel Products are not designed or authorized for use as components in life support appliances, devices or systems where malfunction of a product can reasonably be expected to result in personal injury. Life support devices or systems are devices or systems that (a) are intended for surgical implant into the body or (b) support or sustain life, and whose failure to perform can be reasonably expected to result in a significant injury to the user. A Purchaser's use or sale of Micrel Products for use in life support appliances, devices or systems is at Purchaser's own risk and Purchaser agrees to fully indemnify Micrel for any damages resulting from such use or sale.

Micrel, Inc. ♦ 2180 Fortune Drive ♦ San Jose, CA 95131 ♦ U.S.A.
408-944-0800 (voice) ♦ 408-474-1000 (fax)
<http://www.Micrel.com>

Revision History

Revision	Date	Summary of Changes
1.0	8/15/12	Initial Release

Table of Contents

1.0 Introduction 5

2.0 Board Features 5

3.0 Evaluation Kit Contents..... 5

4.0 Hardware Description 6

 4.1 RMI (Reduced Media Independent Interface)..... 7

 4.2 Jumper Setting & Definition 9

 4.3 Test Point Definition 12

 4.4 RJ-45 Connector 12

 4.5 LED Indicators 12

5.0 Bill of Materials..... 13

List of Figures

Figure 1. KSZ8081RNB Evaluation Board 6

Figure 2. KSZ8081RNB-EVAL interfacing with KSZ8463RLI Evaluation Board 7

List of Tables

Table 1. Connector J2 - RMII Pin Definition 8

Table 2. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Strapping Jumper Definition..... 9

Table 3. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Loopback Jumper Definition 9

Table 4. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Miscellaneous Jumper Definition 10

Table 5. Strapping Pin Definitions for KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Jumpers..... 11

Table 6. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Test Point Definition 12

Table 7. KSZ8081RNB / KSZ8091RNB LED Definition 12

1.0 Introduction

The KSZ8081RNB / KSZ8091RNB is a 10Base-T/100Base-TX Physical Layer Transceiver with an RMII MAC interface. It utilizes a unique mixed-signal design to extend signaling distance while reducing power consumption, and offers HP Auto MDI/MDI-X for reliable detection of and correction for crossover and straight-through cables, eliminating the need to differentiate between crossover and straight-through cables. The KSZ8091RNB supports Energy Efficient Ethernet (EEE) and Wake-On-LAN (WOL), while the KSZ8081RNB does not.

The KSZ8081RNB / KSZ8091RNB comes in a 32-pin, lead-free QFN package and provides an ideal solution for 10Base-T/100Base-TX applications that have tight PCB board space.

The KSZ8081RNB and KSZ8091RNB Eval Boards (KSZ8081RNB-EVAL and KSZ8091RNB-EVAL) provide a convenient platform to evaluate the features of the device. All configuration pins are accessible either by jumpers, test points or interface connectors.

2.0 Board Features

- Micrel KSZ8081RNB or KSZ8091RNB 10Base-T/100Base-TX Physical Layer Transceiver
- RJ-45 Jack for Fast Ethernet cable interface
- HP Auto MDI/MDI-X for automatic detection and correction for straight-through and crossover cables
- RMII (Reduced Media Independent Interface) using an MII connector to interface with a MAC controller
- 2 LED Indicators for status and activity
- Jumpers to configure strapping pins
- Manual Reset Button for quick reboot after re-configuration of strapping pins

3.0 Evaluation Kit Contents

The KSZ8081RNB and KSZ8091RNB Evaluation Kits include the following hardware:

- KSZ8081RNB or KSZ8091RNB Evaluation Board

A design package with the following collaterals that can be downloaded from Micrel's website at <http://www.micrel.com>

- KSZ8081RNB / KSZ8091RNB Eval Board Schematic (PDF and OrCAD DSN file)
- KSZ80x1 (32-QFN) Eval Board Gerber Files (PDF version included)
- KSZ8081RNB / KSZ8091RNB Eval Board User's Guide (this document)
- KSZ8081RNB and KSZ8091RNB IBIS Models

and the KSZ8081MNX / KSZ8081RNB and KSZ8091MNX / KSZ8091RNB Datasheets which are also available from Micrel's website.

4.0 Hardware Description

The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL (shown in Figure 1) come in a compact form factor and plugs directly into other boards with Ethernet MACs that expose the RMII interface through an MII connector. Configuration of the KSZ8081RNB / KSZ8091RNB is accomplished through on-board jumper selections and/or by PHY register access via the MDC/MDIO management pins at the MII connector.




Figure 1. KSZ8081RNB Evaluation Board

Other features include an RJ-45 Jack for Fast Ethernet cable connection, programmable LED indicators for reporting link status and activity, and a manual reset button for quick reboot after re-configuration of strapping pins.

The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL receives +5V DC input power through its MII connector.

4.1 RMII (Reduced Media Independent Interface)

The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL receives power and accesses RMII data and management information from the MII connector J2. Figure 2 shows the KSZ8081RNB-EVAL / KSZ8091RNB-EVAL connected to the Micrel KSZ8463RLI Evaluation Board.




Figure 2. KSZ8081RNB-EVAL interfacing with KSZ8463RLI Evaluation Board

Two RMII clocking modes are available with the KSZ8081RNB / KSZ8091RNB. It may utilize the on-board 25 MHz crystal, connected to XI / XO, and output a 50 MHz REF_CLK signal which is an input to the MAC device to which it is connected. REF_CLK drives pin 9 of the MII connector J2. This is referred to as 25MHz Mode.

Alternatively, the device may be operated in 50MHz mode. In this mode, the KSZ8081RNB / KSZ8091RNB receive the 50 MHz Reference Clock as an input on the XI pin, from pin 12 of the MII connector J2. This clock may be sourced either from the MAC device, or from a separate clock source on the MAC board. The following board changes are required to support 50MHz mode:

1. Remove crystal circuit (Y1, C16, C17) and TXC clock termination (R6).
2. Populate R14 with 0 Ohm and R19 with 33 Ohm to connect RMII 50 MHz reference clock (from J2 pin 12) to U1 pin 9 (XI input).

Additionally, register 1Fh bit [7] must be set to '1' to select 50MHz mode.

The MII Management Interface (MIIM) is conducted thru pins MDC (clock line) and MDIO (data line) on the MII connector J2. MIIM allows upper-layer devices to monitor and control the states of the KSZ8081RNB / KSZ8091RNB. An external device with MDC/MDIO capability can be used to read the PHY status or configure the PHY registers. The MIIM frame format and timing information can be found in the KSZ8081RNB and KSZ8091RNB datasheets and in Clause 22 of the IEEE 802.3 Specification.

The Eval Board has a 40-pin male edge connector that interfaces with and plugs directly into a Fast Ethernet MAC board with the mating AMP 787170-4 (40-pin, right angle, female) connector. Table 1 lists the pin outs for the RMII interface on connector J2.

Pin #	Signal	Pin #	Signal
1	+5V	21	+5V
2	MDIO	22	Ground
3	MDC	23	Ground
4	<not used>	24	Ground
5	<not used>	25	Ground
6	RXD[1]	26	Ground
7	RXD[0]	27	Ground
8	CRSDV	28	Ground
9	<not used>	29	Ground
10	RXER	30	Ground
11	<not used>	31	Ground
12	TXCLK	32	Ground
13	TXEN	33	Ground
14	TXD0	34	Ground
15	TXD1	35	Ground
16	<not used>	36	Ground
17	<not used>	37	Ground
18	<not used>	38	Ground
19	<not used>	39	Ground
20	+5V	40	+5V

Table 1. Connector J2 - RMII Pin Definition

4.2 Jumper Setting & Definition

At power-up, the KSZ8081RNB / KSZ8091RNB are configured using the chip's internal pull-up and pull-down resistors with its default strapping pin values. Jumpers are provided to override the default settings, allowing for quick configuration and re-configuration of the board. To override the default settings, simply select and close the desired jumper setting(s) and toggle the on-board manual reset button (S1) for the new setting(s) to take effect. The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL strapping jumper settings are defined in Table 2 below.

Jumper	Definition	Open (default)	Close						
J3	PHYAD0	1	0						
J4	PHYAD1	0	1						
J5	PHYAD2	0	1						
J6	CONFIG0	<table><tr><th>CONFIG[2:0]</th><th>Mode</th></tr><tr><td>[open, open, close]</td><td>RMII</td></tr><tr><td>[close, open, close]</td><td>RMII Back-to-Back</td></tr></table> All other CONFIG[2:0] settings not listed are reserved (not used).		CONFIG[2:0]	Mode	[open, open, close]	RMII	[close, open, close]	RMII Back-to-Back
CONFIG[2:0]	Mode								
[open, open, close]	RMII								
[close, open, close]	RMII Back-to-Back								
J7	CONFIG1								
J8	CONFIG2								
J9	Isolate Mode	Disable	Enable						
J10	Nway Auto-Negotiation	Enable	Disable						
J11	Forced Speed (KSZ8081 only)	100Base-TX	10Base-T						
J12	Forced Duplex	Half	Full						
J25	Broadcast Off – for PHY Address 0	Broadcast PHY address	Unique PHY address						
J26	PME_N Pin Enable (KSZ8091 only)	Disable	Enable						

Table 2. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Strapping Jumper Definition

The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL has another set of jumpers that may be used to loopback the RMII interface. To loopback, four jumpers must be installed. The individual jumpers are defined in Table 3.

Jumper	RMII Signals	Normal Operation	RMII Loopback Mode
J13	RXDV / TXEN	Open	Close
J14	RXC / TXC	Open	Close
J16	Not used		
J17	RXD1 / TXD1	Open	Close
J18	RXD0 / TXD0	Open	Close
J19	Not used		

Table 3. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Loopback Jumper Definition

The last group of jumpers is defined in Table 4 below. These jumpers are not related to reset strapping, nor to loopback. Two jumpers are used to set the VDDIO voltage, and one jumper is used to route pin 31 as dependent on the device part number.

Note that for the eval board to function, a jumper must be installed on JP3. If pins 1 & 2 of JP3 are closed, then a jumper must also be installed on JP10.

For the KSZ8091RNB, a jumper must be installed on pins 2 & 3 of JP11.

Jumper	Definition	Close pins 1, 2	Close pins 2, 3
JP3	VDDIO voltage selection: 3.3V / low	VDDIO set by JP10	VDDIO = 3.3V
JP10	VDDIO low voltage selection	1.8V_2.5V = 1.8V	1.8V_2.5V = 2.5V
JP11	Pin 31 connection (LED1 or TXER)	For KSZ8081 only (pin 31 = LED1)	For KSZ8091 only (pin 31 = TXER)

Table 4. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Miscellaneous Jumper Definition

Table 5 lists the strapping pin definitions for the KSZ8081RNB-EVAL / KSZ8091RNB-EVAL jumpers.

Jumper	Pin	Pin Name	Pin Function						
J5 J4 J3	15 14 13	PHYAD2 PHYAD1 PHYAD0	The PHY Address is latched at power-up / reset and is configurable to any value from 0 to 7. The default PHY Address is 00001. PHY Address 00000 is enabled only if the B-CAST_OFF strapping pin is pulled high. PHY Address bits [4:3] are always set to '00'.						
J8 J7 J6	18 29 28	CONFIG2 CONFIG1 CONFIG0	The CONFIG[2:0] strap-in pins are latched at power-up / reset and are defined as follows: <table><tr><th>CONFIG[2:0]</th><th>Mode</th></tr><tr><td>001</td><td>RMII</td></tr><tr><td>101</td><td>RMII Back-to-Back</td></tr></table> All other CONFIG[2:0] settings not listed are reserved (not used).	CONFIG[2:0]	Mode	001	RMII	101	RMII Back-to-Back
CONFIG[2:0]	Mode								
001	RMII								
101	RMII Back-to-Back								
J9	20	ISO	ISOLATE mode Pull-up = Enable Pull-down (default) = Disable At the de-assertion of reset, this pin value is latched into register 0h bit 10.						

Jumper	Pin	Pin Name	Pin Function
J11	31	SPEED (KSZ8081 only)	SPEED mode Pull-up (default) = 100Mbps Pull-down = 10Mbps At the de-assertion of reset, this pin value is latched into register 0h bit 13 as the Speed Select, and also is latched into register 4h (Auto-Negotiation Advertisement) as the Speed capability support.
J12	16	DUPLEX	DUPLEX mode Pull-up (default) = Half Duplex Pull-down = Full Duplex At the de-assertion of reset, this pin value is latched into register 0h bit 8 as the Duplex Mode.
J10	30	NWAYEN	Nway Auto-Negotiation Enable Pull-up (default) = Enable Auto-Negotiation Pull-down = Disable Auto-Negotiation At the de-assertion of reset, this pin value is latched into register 0h bit 12.
J25	19	B-CAST_OFF	Broadcast Off – for PHY Address 0 Pull-up = PHY Address 0 is set as a unique PHY address Pull-down (default) = PHY Address 0 is set as a broadcast PHY address At the de-assertion of reset, this pin value is latched by the chip.
J26	22	PME_EN (KSZ8091 only)	PME_N Output Pin for Wake-On-LAN Function Pull-up = Enable Pull-down = Disable At the de-assertion of reset, this pin value is latched into the chip.
N/A	21	NAND_Tree#	NAND Tree Mode Pull-up (default) = Disable Pull-down = Enable At the de-assertion of reset, this pin value is latched by the chip.

Table 5. Strapping Pin Definitions for KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Jumpers

4.3 Test Point Definition

The KSZ8081RNB-EVAL / KSZ8091RNB-EVAL has four test points. They are defined in the following table.

Test Point	Definition
TP1	Pin 21 (with external pull-up) KSZ8081: Interrupt KSZ8091: Interrupt or PME_N2
TP2	Ground
TP3	Ground
TP7	Pin 30 KSZ8081: LED0 KSZ8091: LED0 or PME_N1

Table 6. KSZ8081RNB-EVAL / KSZ8091RNB-EVAL Test Point Definition

4.4 RJ-45 Connector

The RJ-45 Connector (J1) is a TDK TLA-6T718A or similar integrated magnetic jack. It connects to standard CAT-5 Ethernet cable to interface with 10Base-T / 100Base-TX Ethernet devices.

4.5 LED Indicators

A dual LED indicator (LED1) is located adjacent to the RJ-45 Connector. The top LED and bottom LED are connected to LED1 (pin 31) and LED0 (pin 30) respectively.

The two LEDs are programmable to LED mode '00' or '01' via register 1Fh bits [5:4], and are defined in the following table.

LED Mode	LED1 (pin 31)			LED0 (pin 30)		
00						
	Speed	Pin State	LED Definition	Link/ Activity	Pin State	LED Definition
	10Base-T	H	OFF	No Link	H	OFF
	100Base-Tx	L	ON	Link	L	ON
				Activity	Toggle	Blinking
01						
	Activity	Pin State	LED Definition	Link	Pin State	Definition
	No Activity	H	OFF	No Link	H	OFF
	Activity	Toggle	Blinking	Link	L	ON
10	Reserved – not used			Reserved – not used		
11	Reserved – not used			Reserved – not used		

Table 7. KSZ8081RNB / KSZ8091RNB LED Definition

5.0 Bill of Materials

KSZ8081RNB / KSZ8091RNB Eval Board, Schematic Revision 1.0

Item	Quantity	Reference	Description	Package
1	2	C1,C2	47uF / Tantalum	B-size
2	1	C3	22uF / Tantalum	B-size
3	10	C4,C5,C7,C10,C11,C12, C49,C51,C57,C58	0.1uF	0603
4	4	C6,C8,C48,C50	10uF / Tantalum	A-size
5	1	C9	2.2uF	A-size
6	2	C16,C17	22pF	0603
7	1	C52	470pF	0603
8	1	D1	1N4148	DO-35 / axial lead
9	2	FB1,FB7	Ferrite Bead	1206
10	1	J1	RJ-45 Mag Jack	thru hole / PC mount
11	1	J2	Male MII Connector	PCB edge mount
12	18	J3,J4,J5,J6,J7,J8,J9,J10, J11,J12,J13,J14,J16 J17,J18,J19,J25,J26	Header 2X1	thru hole / 0.1" pitch
13	3	JP3,JP10,JP11	Header 3X1	thru hole / 0.1" pitch
14	1	LED1	LEDx2 / Green	thru hole / 0.1" pitch
15	1	R1	100K	0603
16	1	R2	10K	0603
17	9	R3,R25,R26,R27,R28, R29,R30,R102,R103	4.7K	0603
18	10	R4,R5,R6,R7,R8,R9,R16, R17,R20,R21	33	0603
19	1	R112	680	0603
20	1	R15	6.49K	0603
21	2	R22,R24	220	0603
22	5	R18,R23,R31,R32,R33	1K	0603
23	2	R111,R113	1.5K	0603
24	1	S1	SW PUSHBUTTON	SMT
25	4	TP1,TP2,TP3,TP7	TestPoint	thru hole / 0.1" pitch
26	1	U1	KSZ8081RNB or KSZ8091RNB	32-pin QFN
27	1	U2	MIC5216-3.3YM5	SOT-23-5
28	1	U7	MIC5207YM5	SOT-23-5
29	1	Y1	Xtal 25MHz +/-50ppm	cylinder