

NCP4305 Synchronous Rectification Evaluation Board User's Manual



EVAL BOARD USER'S MANUAL

SMPS Type	Supply Voltage	Reverse Voltage	Effective Resistance
LLC	5–35 V	40 V	0.9 mΩ

This evaluation board user's manual describes a high efficiency synchronous rectification evaluation board that can easily replace a secondary side rectification diode in an SMPS.

The NCP4305 features a very precise 0 mV turn-off comparator that supports even very low current flowing through the MOSFET even when very low $R_{DS(ON)}$ synchronous MOSFETs is used.

- Precise Turn-off Comparator
- Wide Input Voltage Range
- High Operation Frequency
- Strong MOSFET Driver
- High Efficiency
- Adjustable Minimum On and Off Times
- Light Load Detection Feature
- Capable to Operate in Positive and Negative Branch
- Small size



Figure 1. NCP4305 Evaluation Board

Connection Diagram




Figure 2. Possible Connections in to Circuit

The evaluation board can be connected in circuit where the rectification diode is in the positive or negative branch. When connection to a positive branch is used, it is necessary to use an external power supply (or auxiliary winding with

rectification) to provide power to the evaluation board. VCC should be referenced to A1 or A2 points. When LLD function is used it is needed to connect LLD1 pin with opposite side rectifier cathode.

Evaluation Board Schematic




Figure 3. Schematic of the NCP4305

The evaluation board was designed to support a minimal external component count implementation. C1 and C2 are decoupling capacitors. They should be placed as close as possible to the VCC and GND pins. Resistors R_{MIN_TON} and R_{MIN_TOFF} are used to set the protection interval when the synchronous MOSFET is turned on and off. Resistor R_{MIN_TOFFM} is placed there to support a situation when an external circuit provides control for minimum off-time modulation. This is needed only in situations when the minimum off-time cannot be set across the whole range of power supply operation. Resistor R_{TRIG_PD} is only pull down for TRIG pin and R_{TRIG} is only protection resistor. A position for a gate resistor R_G is provided in case there is a need to slow down the MOSFET switching process. The turn-off (and also the turn-on) threshold can be lowered when resistor R_{CS} is used. Components C_{SNB} , R_{SNB1} and R_{SNB2} form a snubber circuit.

LLD circuit consists of C_{LLD1} , C_{LLD2} , R_{LLD1} , R_{LLD2} , R_{LLD3} and D4. Purpose of circuit is to estimate output power. This can be done in two ways. The first is to measure duty cycle of skip burst. LLD circuit time constant is high and it filters and averages duty cycle ratio. This is good for systems which transfer low energy during skip each switch cycle. When duty cycle of skip bursts is low NCP4305 enters disable mode to save energy, when it is higher SR controller

starts to operate and SR transistor gate voltage is modulated according to skip duty cycle. The second option is for system which transfers lot of energy in few first pulses in skip and then transferred energy is minimal. In this case LLD circuit time constant is low and R_{LLD3} resistance is close to 0. LLD pin voltage drops down in first switching pulse in skip mode and NCP4305 wakes up fast and allows using fully open SR transistor. When skip burst ends, LLD voltage goes high and if time between skip bursts is long enough NCP4305 enters disable mode to save energy.

Circuit Layout

The PCB consists of a 2 layer FR4 board with 35 μ m copper cladding. All components are surface mount and most of the components that may require adjustment are on the same side and use 1206 values for easy rework. Critical component such as blocking capacitors C1 and C2 have to be placed carefully near the IC. The synchronous driver path to the MOSFETs was done with very low resistance and parasitic inductance to minimize emissions and minimize turn-on and turn-off times. The same is true for the CS pin. For the CS pin, a kelvin contact was done to be able to sense the voltage directly at the drain. Improper connection of the GND and CS connects can impact the turn-off process especially when a very low $R_{DS(on)}$ MOSFETs are used.

NCP4305DGEVB




Figure 4. Top Layer




Figure 5. Bottom Layer




Figure 6. Top Side Components

5

NCP4305DGEVB

Table 2. BILL OF MATERIALS FOR NCP4305 PUT-IN BOARD SO-8FL (Note 1)

Parts	Qty	Description	Value	Tolerance	Footprint	Manufacturer	Manufacturer Part Number	Substitution Allowed
C1	1	Ceramic Capacitor	100 nF	10%	1206	Kemet	C1206X104K5RACTU	Yes
C2	1	Ceramic Capacitor	1 μ F/50 V	10%	1206	Kemet	C1206X105K5RACTU	Yes
C _{LLD1} , C _{LLD2}	2	–	NU	–	1206	–	–	Yes
C _{SNB}	1	Ceramic Capacitor	3.9 nF	–	1206	Kemet	C1206C392K5RACTU	Yes
D1, D4	2	Switching Diode	BAS20HT1G	–	SOD-323	ON Semiconductor	BAS20HT1G	Yes
IC1	1	Secondary Side Synchronous Rectification Controller	NCP4305D	–	SOIC-08	ON Semiconductor	NCP4305DDR2G	No
M1, M2	2	N-Channel Power MOSFET	NVMFS5830NL	–	SO-8FL	ON Semiconductor	NVMFS5830NLT1G	Yes
R _{CS} , R _G	2	Resistor SMD	0 Ω	5%	1206	Yageo	RC1206JR-070RL	Yes
R _{G_PD}	1	Resistor SMD	10 k Ω	1%	1206	Yageo	RC1206FR-0710KL	Yes
R _{LLD_PD} , R _{TRIG} , R _{TRIG_PD}	3	Resistor SMD	1 k Ω	1%	1206	Yageo	RC1206FR-071KL	Yes
R _{LLD1} , R _{LLD2} , R _{LLD3} , R _{SNB2} , R _{MIN_TOFFML}	5	Resistor SMD	NU	–	1206	–	–	Yes
R _{MIN_TOFF}	1	Resistor SMD	22 k Ω	1%	1206	Yageo	RC1206FR-0722KL	Yes
R _{MIN_TON}	1	Resistor SMD	4.7 k Ω	1%	1206	Yageo	RC1206FR-074K7L	Yes
R _{SNB1}	1	Resistor SMD	15 Ω	1%	1206	Yageo	RC1206FR-0715RL	Yes

1. All parts are Pb-Free

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is as such not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and should as such only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

The board is delivered "AS IS" and without warranty of any kind including, but not limited to, that the board is production-worthy, that the functions contained in the board will meet your requirements, or that the operation of the board will be uninterrupted or error free. ON Semiconductor expressly disclaims all warranties, express, implied or otherwise, including without limitation, warranties of fitness for a particular purpose and non-infringement of intellectual property rights.

ON Semiconductor reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by ON Semiconductor shall not constitute any representation or warranty by ON Semiconductor, and no additional obligations or liabilities shall arise from ON Semiconductor having provided such information or services.

The boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. Should you purchase or use the board for any such unintended or unauthorized application, you shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by ON Semiconductor to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

ON Semiconductor does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: ON Semiconductor shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if ON Semiconductor is advised of the possibility of such damages. In no event shall ON Semiconductor's aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

For more information and documentation, please visit www.onsemi.com.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative