



# LV5103LP — Bi-CMOS LSI Cell Phone Power Supply IC

## Overview

The LV5103LP is a cell phone power supply IC.

## Functions

- Single step-down DC-DC converter channel
- Eight series regulator channels
- Built-in thermal shutdown circuit

## Features

- Low power dissipation
- Built-in shorting protection circuit

## Specifications

### Maximum Ratings at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Maximum supply voltage	V <sub>CC</sub> max		6	V
Allowable power dissipation	P <sub>d</sub> max	Mounted on a circuit board.*	1100	mW
Operating temperature	T <sub>op</sub> r		-30 to +75	°C
Storage temperature	T <sub>stg</sub>		-40 to +125	°C

\* Specified circuit board : 40×50×0.8mm<sup>3</sup> : 4-layer (2S2P) glass epoxy printed circuit board

### Operating Conditions at Ta = 25°C

Parameter	Symbol	Conditions	Ratings	Unit
Supply voltage	V <sub>CC</sub>		3.2 to 4.5	V

- Any and all SANYO Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your SANYO Semiconductor representative nearest you before using any SANYO Semiconductor products described or contained herein in such applications.
- SANYO Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all SANYO Semiconductor products described or contained herein.

# LV5103LP

## Electrical Characteristics

T<sub>a</sub> = 25°C, V<sub>BAT</sub> = 3.7V, V<sub>BATL</sub> = 2.4V, unless otherwise specified.

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
<b>[Analog block] Current drain</b>						
Current drain 1	I <sub>CC1</sub>	With LD01 and V <sub>BATDET</sub> operating		8	16	µA
Current drain 2	I <sub>CC2</sub>	With LD01, LD02, LD05, LD06, LD07, and LD08 operating. PS mode		50	75	µA
Current drain 3	I <sub>CC3</sub>	With all LD0n channels operating, DC-DC operation		6	10	mA
<b>[Switching Regulator Block] DC/DC1</b>						
Output voltage 1	V <sub>OSW1</sub>	I <sub>O</sub> = 500mA	2.25	2.4	2.55	V
Output current	I <sub>SW1</sub>		800			mA
Efficiency 1	EF1	I <sub>O</sub> = 150mA		86		%
Efficiency 2	EF2	I <sub>O</sub> = 500mA		79		%
Oscillator frequency	F <sub>osc1</sub>		1	1.2	1.4	MHz
<b>LDO1</b>						
Output voltage	V <sub>OR1</sub>	I <sub>O</sub> = 10mA	1.47	1.5	1.53	V
Output current	I <sub>M1</sub>		30			mA
Load regulation	V <sub>L1</sub>	I <sub>O</sub> = 1 to 30mA		10	75	mV
Line regulation	V <sub>R1</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 20mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T1</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 10mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL1</sub>	I <sub>O</sub> = 10mA, V <sub>RR</sub> = -20dBV, f <sub>RR</sub> = 120Hz		65		dB
Output noise voltage	V <sub>ON1</sub>	I <sub>O</sub> = 10mA, 10Hz < f < 100kHz		60		µVrms
<b>LDO2</b>						
Output voltage	V <sub>OR2</sub>	I <sub>O</sub> = 30mA	2.79	2.85	2.91	V
Output current	I <sub>M2</sub>		200			mA
Load regulation	V <sub>L2</sub>	I <sub>O</sub> = 1 to 200mA		20	75	mV
Line regulation	V <sub>R2</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 130mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T2</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL2</sub>	I <sub>O</sub> = 30mA, V <sub>RR</sub> = -20dBV, f <sub>RR</sub> = 120Hz		65		dB
Output noise voltage	V <sub>ON2</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		50		µVrms
<b>LDO2 PS MODE</b>						
Output voltage	V <sub>OR2P</sub>	I <sub>O</sub> = 30mA	2.76	2.85	2.94	V
Output current	I <sub>M2P</sub>		200			mA
Load regulation	V <sub>L2P</sub>	I <sub>O</sub> = 1 to 200mA		20	75	mV
Line regulation	V <sub>R2P</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 130mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T2P</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL2P</sub>	I <sub>O</sub> = 30mA, V <sub>RR</sub> = -20dBV, f <sub>RR</sub> = 120Hz		60		dB
Output noise voltage	V <sub>ON2P</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		60		µVrms
<b>LDO3</b>						
Output voltage	V <sub>OR3</sub>	I <sub>O</sub> = 30mA	2.79	2.85	2.91	V
Output current	I <sub>M3</sub>		150			mA
Load regulation	V <sub>L3</sub>	I <sub>O</sub> = 1 to 150mA		20	75	mV
Line regulation	V <sub>R3</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 100mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T3</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL3</sub>	I <sub>O</sub> = 30mA, V <sub>RR</sub> = -20dBV, f <sub>RR</sub> = 120Hz		65		dB
Output noise voltage	V <sub>ON3</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		50		µVrms
<b>LDO3B SW</b>						
Switch on-resistance	RSW3	I <sub>O</sub> = 50mA, SWCTL : HIGH		1.5	2.5	Ω
Switch leakage current	ISW3	SWCTL : LOW		0	3	µA

Continued on next page.

# LV5103LP

Continued from preceding page.

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
<b>LDO4</b>						
Output voltage 1	$V_{OR41}$	$I_O = 30mA$	3.03	3.1	3.17	V
Output voltage 2	$V_{OR42}$	$I_O = 200mA$	3	3.1	3.2	V
Output current 1	$I_{M41}$		450			mA
Output current 2	$I_{M42}$	$V_{BAT} = 3.4V, V_{OUT} \geq 3V$	300			mA
Load regulation 1	$V_L4$	$I_O = 1$ to $300mA$		30	100	mV
Load regulation 2	$V_{L4L}$	$V_{BAT} = 3.4V, I_O = 1$ to $250mA$		50	100	mV
Line regulation 1	$V_R4$	$V_{BAT} = 3.4$ to $4.5V, I_O = 200mA$		10	60	mV
Output voltage temperature coefficient	$\Delta V_{T4}$	$T_a = -30$ to $75^{\circ}C, I_O = 30mA$		$\pm 100$		ppm/ $^{\circ}C$
Ripple rejection ratio	$V_{RL4}$	$I_O = 30mA, VRR = -20dBV, fRR = 120Hz$		65		dB
Output noise voltage	$V_{ON4}$	$I_O = 30mA, 10Hz < f < 100kHz$		50		$\mu V_{rms}$
<b>LDO5</b>						
Output voltage	$V_{OR5}$	$I_O = 30mA$	3.23	3.3	3.37	V
Output current 1	$I_{M51}$		150			mA
Output current 2	$I_{M52}$	$V_{BAT} = 3.4V, V_{OUT} \geq 3V$	150			mA
Load regulation 1	$V_L5$	$I_O = 1$ to $150mA$		75	150	mV
Load regulation 2	$V_{L5L}$	$V_{BAT} = 3.4V, I_O = 1$ to $50mA$		75	150	mV
Line regulation 1	$V_R5$	$V_{BAT} = 3.4$ to $4.5V, I_O = 100mA$		10	60	mV
Output voltage temperature coefficient	$\Delta V_{T5}$	$T_a = -30$ to $75^{\circ}C, I_O = 30mA$		$\pm 100$		ppm/ $^{\circ}C$
Ripple rejection ratio	$V_{RL5}$	$I_O = 30mA, VRR = -20dBV, fRR = 120Hz$		65		dB
Output noise voltage	$V_{ON5}$	$I_O = 30mA, 10Hz < f < 100kHz$		50		$\mu V_{rms}$
<b>LDO5 PS MODE</b>						
Output voltage	$V_{OR5P}$	$I_O = 30mA$	3.2	3.3	3.4	V
Output current	$I_{M5P}$		150			mA
Load regulation 1	$V_{L5P1}$	$I_O = 1$ to $150mA$		75	150	mV
Load regulation 2	$V_{L5P2}$	$V_{BAT} = 3.4V, I_O = 1$ to $50mA$		75	150	mV
Line regulation 1	$V_R5P$	$V_{BAT} = 3.4$ to $4.5V, I_O = 100mA$		10	60	mV
Output voltage temperature coefficient	$\Delta V_{T5P}$	$T_a = -30$ to $75^{\circ}C, I_O = 30mA$		$\pm 100$		ppm/ $^{\circ}C$
Ripple rejection ratio	$V_{RL5P}$	$I_O = 30mA, VRR = -20dBV, fRR = 120Hz$		60		dB
Output noise voltage	$V_{ON5P}$	$I_O = 30mA, 10Hz < f < 100kHz$		60		$\mu V_{rms}$
<b>LDO6</b>						
Output voltage	$V_{OR6}$	$I_O = 30mA$	1.47	1.5	1.53	V
Output current	$I_{M6}$		200			mA
Load regulation	$V_{L6}$	$I_O = 1$ to $200mA$		20	75	mV
Line regulation 1	$V_R6$	$V_{BAT} = 3.1$ to $4.5V, I_O = 130mA$		10	60	mV
Output voltage temperature coefficient	$\Delta V_{T6}$	$T_a = -30$ to $75^{\circ}C, I_O = 30mA$		$\pm 100$		ppm/ $^{\circ}C$
Ripple rejection ratio	$V_{RL6}$	$I_O = 30mA, VRR = -20dBV, fRR = 120Hz$		65		dB
Output noise voltage	$V_{ON6}$	$I_O = 30mA, 10Hz < f < 100kHz$		50		$\mu V_{rms}$
<b>LDO6 PS MODE</b>						
Output voltage	$V_{OR6P}$	$I_O = 30mA$	1.45	1.5	1.55	V
Output current	$I_{M6P}$		10			mA
Load regulation	$V_{L6P}$	$I_O = 1$ to $10mA$		10	75	mV
Line regulation 1	$V_R6P$	$V_{BAT} = 3.1$ to $4.5V, I_O = 10mA$		10	60	mV
Output voltage temperature coefficient	$\Delta V_{T6P}$	$T_a = -30$ to $75^{\circ}C, I_O = 30mA$		$\pm 100$		ppm/ $^{\circ}C$
Ripple rejection ratio	$V_{RL6P}$	$I_O = 30mA, VRR = -20dBV, fRR = 120Hz$		60		dB
Output noise voltage	$V_{ON6P}$	$I_O = 30mA, 10Hz < f < 100kHz$		60		$\mu V_{rms}$

Continued on next page.

# LV5103LP



Continued from preceding page.

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
<b>LDO7</b>						
Output voltage	V <sub>OR7</sub>	I <sub>O</sub> = 30mA	1.76	1.8	1.84	V
Output current	I <sub>M7</sub>		150			mA
Load regulation	V <sub>L7</sub>	I <sub>O</sub> = 1 to 150mA		75	150	mV
Line regulation 1	V <sub>R7</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 100mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T7</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL7</sub>	I <sub>O</sub> = 30mA, VRR = -20dBV, fRR = 120Hz		65		dB
Output noise voltage	V <sub>ON7</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		50		µVrms
<b>LDO7 PS MODE</b>						
Output voltage	V <sub>OR7P</sub>	I <sub>O</sub> = 30mA	1.74	1.8	1.86	V
Output current	I <sub>M7P</sub>		10			mA
Load regulation	V <sub>L7P</sub>	I <sub>O</sub> = 1 to 10mA		75	150	mV
Line regulation 1	V <sub>R7P</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 10mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T7P</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL7P</sub>	I <sub>O</sub> = 30mA, VRR = -20dBV, fRR = 120Hz		60		dB
Output noise voltage	V <sub>ON7P</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		60		µVrms
<b>LDO8</b>						
Output voltage 1	V <sub>OR81</sub>	I <sub>O</sub> = 30mA	1.17	1.2	1.23	V
Output voltage 2	V <sub>OR82</sub>	I <sub>O</sub> = 200mA	1.13	1.2	1.27	V
Output current 1	I <sub>M81</sub>		500			mA
Output current 2	I <sub>M82</sub>	V <sub>BAT</sub> = 3.4V, V <sub>OUT</sub> ≥ 1.1V	500			mA
Load regulation	V <sub>L8</sub>	I <sub>O</sub> = 1 to 500mA		30	70	mV
Line regulation 1	V <sub>R8</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 330mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T8</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL8</sub>	I <sub>O</sub> = 30mA, VRR = -20dBV, fRR = 120Hz		65		dB
Output noise voltage	V <sub>ON8</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		50		µVrms
<b>LDO8 PS MODE</b>						
Output voltage	V <sub>OR8P</sub>	I <sub>O</sub> = 30mA	1.16	1.2	1.24	V
Output current	I <sub>M8P</sub>		10			mA
Load regulation	V <sub>L8P</sub>	I <sub>O</sub> = 1 to 10mA		30	100	mV
Line regulation 1	V <sub>R8P</sub>	V <sub>BAT</sub> = 3.1 to 4.5V, I <sub>O</sub> = 10mA		10	60	mV
Output voltage temperature coefficient	ΔV <sub>T8P</sub>	T <sub>a</sub> = -30 to 75°C, I <sub>O</sub> = 30mA		±100		ppm/°C
Ripple rejection ratio	V <sub>RL8P</sub>	I <sub>O</sub> = 30mA, VRR = -20dBV, fRR = 120Hz		60		dB
Output noise voltage	V <sub>ON8P</sub>	I <sub>O</sub> = 30mA, 10Hz < f < 100kHz		60		µVrms
<b>DET24</b>						
Low-level detection voltage	VDL1		2.35	2.4	2.45	V
High-level detection voltage	VDH1		2.62	2.7	2.78	V
<b>VBATDET</b>						
Low-level detection voltage	VDL2		2.3	2.4	2.5	V
High-level detection voltage	VDH2		3.1	3.2	3.3	V
<b>BVLT Switch</b>						
BVLT switch on-resistance	R <sub>SWBV</sub>	I <sub>O</sub> = 3mA, BVLTON : HIGH		300	400	Ω
BVLT switch leakage current	I <sub>SWBV</sub>	BVLTON : LOW		0	1	µA
<b>Control Pins</b>						
High level 1	VH1	RFPDN, ADPTDETIN, PWRHOLD, POWERSAVE, SWCTL, BVLTON, STCLR	1.5		VBAT	V
Low level 1	VL1	RFPDN, ADPTDETIN, PWRHOLD, POWERSAVE, SWCTL, BVLTON, STCLR	0		0.3	V
High level 2	VH2	PWRKEY	VBAT×0.8		VBAT	V
Low level 2	VL2	PWRKEY	0		VBAT×0.2	V

## Package Dimensions

unit : mm (typ)

3302A



## Control Pin Functions

### Power Supply Control

RFPDN	ADPTDET	PWRKEY	PWRHOLD	LDO1	LDO2, 5, 6, 7, 8	LDO3, 4
Low	Low	Low	Low	On	Off	Off
Low	High			On	On	Off
Low		High		On	On	Off
Low			High	On	On	Off
High	Low	Low	Low	On	Off	Off
High	High			On	On	On
High		High		On	On	On
High			High	On	On	On

(ON/OFF1) (ON/OFF2)

### PS Mode


PWRSAVE	Mode
Low	PS mode
High	Normal mode

### LDO3 Output Switch


SWCTL	Mode
Low	Switch off
High	Switch on

### BVLT Output

BVLTON	Mode
Low	Switch off
High	Switch on

**Pin Assignment**

## Block Diagram



The three power supply pins VBAT1, VBAT2, and VBAT3 must be shorted together externally.

The three ground pins GNDM, PGND, and GNDSWREG must be shorted together externally and must always be at a potential that is the lowest potential in the system.






## Equivalent Circuit Block Diagram

Pin No.	Pin	Functions	Equivalent Circuit
1 16 19 37 39	STCLR PWRHOLD RFPDN PWRSAVE ADPTDETIN	Input pins	
29 21 2	VBAT1 VBAT2 VBAT3	Power supply pins	
3 9 11	VBATL8 VBATL6 VBATL7	VBATL pins The M1 transistor is only present in the VBATL8 circuit.	
4 5 7 8 10 20 22 23 24 27 28 30 31	LDO8O LDO8S LDO6S LDO6O LDO7O LDO5O LDO4O LDO4S LDO1O LDO3S LDO3O LDO2O LDO2S	LDO output pins The LDO*O pins for LDO1, LDO5, and LDO7 are shorted internally in the IC to the corresponding LDO*S pin.	
6	STATUS	STATUS pin	

Continued on next page.

# LV5103LP






Continued from preceding page.

Pin No.	Pin	Functions	Equivalent Circuit
12	FBIN	Feedback resistor connection for the switching regulator block	
14	RREF	RREF reference voltage	
15	BGR	BGR reference voltage	
17	RKEYDET	PKEYDET pin	
18	PWRKEY	PWRKEY pin	

Continued on next page.

# LV5103LP

Continued from preceding page.

Pin No.	Pin	Functions	Equivalent Circuit
25 26	SWCTL LDO3B	SWCTL pin LDO3B pin	
32	DELAY	DELAY pin	
33	RESET	RESET pin	
34 36	BVLT BVLTON	BVLT and BVLTON pins	
40	SWOUT	SWREG output block	

- Specifications of any and all SANYO Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- SANYO Semiconductor Co., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all SANYO Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of SANYO Semiconductor Co., Ltd.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the SANYO Semiconductor product that you intend to use.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. SANYO Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

This catalog provides information as of January, 2007. Specifications and information herein are subject to change without notice.