


REVISION HISTORY			
ECO	REV	DESCRIPTION	DATE
	2	PROTO	06/08/04
APPROVED			



NOTES: UNLESS OTHERWISE SPECIFIED,

- ARTWORK P/N DC811A REV 2.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS AND 1 OZ. COPPER ON TWO INTERNAL LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER. COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH YELLOW NON-CONDUCTIVE INK. PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

SIZE	QTY	SYM	PLTD	TOL
10	41	+	YES	+/-0.003
35	26	X	YES	+/-0.003
70	2	□	NO	+/-0.005
94	10	◇	YES	+/-0.01

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± °
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M – 1994

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

CONTRACT NO

APPROVALS

DRAWN MEI

CHECKED

APPROVED

ENGINEER

DATE

06/08/04

LINEAR TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035
Phone: (408)432-1900
Fax: (408)434-0507

TITLE

FAB, LT3027EDD, DUAL OUTPUT LOW NOISE
LDO REGULATOR

SIZE

CAGE CODE

DWG NO

REV

DC811A

DC811A

2

SCALE

1/1

FILENAME: DC811A-2.PCB

SHEET

1 OF 1