

Filename: PMP5732_RevB bom.xls

Date: 08/02/2011

PMP5732 REV_B BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	C1	0.22uF	Capacitor, Polypropelene film, 310VAC	1.024 X 0.335 inch	BFC233820224	Vishay
1	C2	10nF	Capacitor, Ceramic, 500V, X7R, 10%	1812		
1	C3	0.22uF	Capacitor, X2 Class, 0.22uF, 275V, 20%	0.709 x 0.236 inch	R46KI322050M2M	Kemet (Arcotronics)
3	C4	1200uF	Capacitor, Aluminum Electrolytic, 1200uF, 50V	0.492 inch	EEUFC1H122S	Panasonic
	C5	1200uF	Capacitor, Aluminum Electrolytic, 1200uF, 50V	0.492 inch	EEUFC1H122S	Panasonic
	C101	1200uF	Capacitor, Aluminum Electrolytic, 1200uF, 50V	0.492 inch	EEUFC1H122S	Panasonic
3	C6	.1u	Capacitor, Ceramic, 16-V, [temp], [tol]	0805	std	muRata
2	C7	100uF	Capacitor, Aluminum Electrolytic, 100uF, 35V	0.248 inch	EKZM350ELL101MF11D	Nippon ChemiCon
1	C8	47uF	Capacitor, Aluminum Electrolytic, 47uF, 35V	0.197 inch	EEEFK1V470AP	Panasonic
	C9	.1u	Capacitor, Ceramic, 16-V, [temp], [tol]	0805	std	muRata
1	C10	470pF	CAP 300VAC X1/Y2	0.236 x 0.315 inch	VY2471K29Y5SS63V7	Vishay
1	C11	2.2nF	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	C12	56uF	Capacitor, Aluminum Electrolytic, 56uF, 35V	0.248 inch	EKY-250Exx101MF11D	Nippon ChemiCon
1	C13	10pF	Capacitor, Ceramic, 50V, NP0, 10%	0603	Std	muRata
	C14	.1u	Capacitor, Ceramic, 16-V, [temp], [tol]	0805	std	muRata
1	C15	DNP	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	C16	3.3uF	Capacitor, Ceramic, 16V, X7R, 10%	805	Std	Std
	C17	100uF	Capacitor, Aluminum Electrolytic, 100uF, 35V	0.248 inch	EKZM350ELL101MF11D	Nippon ChemiCon
1	C18	220nF	Capacitor, Ceramic, 50V, X7R, +/-10%	603	std	std
1	D1	KBP06G	Diode, Bridge Rectifier, 1.5A, 600V	0.580 x 0.145 inch	KBP06G	Diodes
2	D2	BYG10J	Diode, Standard Rectifier,1.5A, 600V	SMA	BYG10J	Vishay
	D3	BYG10J	Diode, Standard Rectifier,1.5A, 600V	SMA	BYG10J	Vishay
1	D4	US1K	Diode Ultrafast, 1-A, 800-V	SMA	US1K	Diodes Inc.
1	D5	MUR1020CT	Diode, Dual Ultrafast Rectifier, 200V, 10A	TO-220	MUR1020CT	On Semi
2	D6	MURA120T3	Diode, Rectifier, 1A, 200-V	SMA	MURA120T3	ON
1	D7	18V	Diode, Zener, 1W, 18V	SMA	SMAZ18-13	Diodes Inc.
	D8	MURA120T3	Diode, Rectifier, 1A, 200-V	SMA	MURA120T3	ON
1	D9	39V	Diode, Zener, 39-V	SOT23	MMBZ5259	ON
1	D10	MBR0520L	Diode, Schottky, 0.5A, 20V	SOD-123	MBR0520L	Fairchild
1	D11	8.2v	Diode, Zener, 8.2-V, yy-mA, zz-mW, q%	SOT23	BZX84C8V2	On Semiconductor

3	D12	BAS16	Diode, Switching, 75V, 200mA	SOT23	BAS16LT1	On Semiconductor
	D13	BAS16	Diode, Switching, 75V, 200mA	SOT23	BAS16LT1	On Semiconductor
1	F1	1A/250V	Fuse, TR5 Series, 1A, 250V	0.335	3701100041	Wickmann
1	J1	ED555/2DS	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25 inch	ED555/2DS	OST
1	L1	1mH	Inductor, SMT, 0.8A, zzmilohm	0.51x 0.37 inch	DO3340P-105ML	Coilcraft
1	L2	20mH	Inductor, 0.5 A, 540 milliohm	0.512 x 0.728 inch	744822120	WE
1	Q1	SPP11N80	MOSFET, Nchan, 650V, 8.5A, 930 millohm	TO-220AB	IRFB9N65A	Vishay
1	Q2	3904	Bipolar, NPN, xx-V, yy-mA, zz-W	SOT23	MMBT3904	
2	R1	100K	Resistor, Chip, ¼ W, 5%	1210	STD	STD
2	R2	22K	Resistor, Metal -Mite, 2W, ±1%	{Size}	std	Std
	R3	22K	Resistor, Metal -Mite, 2W, ±1%	{Size}	std	Std
	R4	100K	Resistor, Chip, ¼ W, 5%	1210	STD	STD
1	R5	100K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R6	0.022	Resistor, Chip,1/2W, 1%	1210	STD	STD
1	R7	348	Resistor, Chip, 1/8W, 5%	1206	Std	Std
1	R8	2.2	Resistor, Chip, 1/8W, 5%	1206	Std	Std
2	R9	750k	Resistor, Chip, ¼ W, 5%	1210	STD	STD
3	R10	1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R11	75K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R12	1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R13	6.98K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R14	750k	Resistor, Chip, ¼ W, 5%	1210	STD	STD
	R15	75K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R16	10	Resistor, Chip, 1/10-W, 1%	0805	Std	Std
	R17	2K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R18	10K	Resistor, Chip, 1/10W, yy%	0805	Std	Std
1	R19	10K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R20	68.1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R21	332	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R22	0.5	Resistor, Chip, 0.5-Ohms, 1-W, 1%	2512	Std	Std
1	R23	1.5k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
3	R24	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R25	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R26	2.49k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R27	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R102	TBD	Resistor, Chip, 1/10-W, 1%	0805	Std	Std

1	T1	G084231LF	Transformer, Flyback, 10±%	0.964 X 1.240 inch	G084231LF	GCI
5	TP1	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP2	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP3	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP4	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP5	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	U1	TL103WID	IC, Dual Op Amp With Internal Reference	SO8	TL103WID	TI
1	U2	UCC28810D	IC, LED LIGHTING POWER CONTROLLER	SO8	UCC28810D	TI
1	U3	TCMT1107	IC, Photocoupler, CTR = 80% - 160%	MF4	TCMT1107	Vishay

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
 2. These assemblies must be clean and free from flux and all contaminants.
Use of no clean flux is not acceptable.
 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
 4. Ref designators marked with an asterisk ('**') cannot be substituted.
All other components can be substituted with equivalent MFG's components.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated