

PMP5997_REVC BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
9	C1, C2, C9, C15, C17, C18, C19, C22, C23	1uF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
1	C10	0.047uF	Capacitor, Ceramic, 250-V, X7R	1206	C3216X7R2E473M	TDK
1	C100	0.068uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H683K	TDK
3	C11, C12, C24	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H104K	TDK
1	C13	100uF	Capacitor, Aluminum, 25V, ZL Series	0.200 * 0.435 inch	25V ZL 100uF	Rubycon
1	C14	1000pF	Capacitor, Ceramic, 2kV, C0G, 10%	1812	Std	Std
1	C16	47pF	Capacitor, Ceramic, 50V, C0G, 10%	0603	C1608C0G1H470K	TDK
1	C20	0.033uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H333K	TDK
1	C21	220pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H221K	TDK
1	C25	1000pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H102K	TDK
1	C26	2200pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H222K	TDK
1	C27	4.7uF	Capacitor, Ceramic, 16V, X7R, 15%	0805	Std	Std
4	C3, C4, C5, C6	2.2uF	Capacitor, Ceramic, 100-V, X7R, 20%	1210	C3225X7R2A225M	TDK
2	C7, C8	680uF	Capacitor, Conductive Polymer, 6.3V	0.394 inch	6SEPC680M	Sanyo
1	D1	MBRA340	Diode, Schottky, 3-A, 40-V	SMA	MBRA340LT3	ON Semi
1	D2	5.1V	Diode, Zener, 5.1-V	SOT23	BZX84C5V1LT1	ON Semiconductor
2	D3, D6	DNP	Do Not Populate	SOD-123	N/A	N/A
5	D4, D5, D7, D9, D10	MMSD914	Diode, Switching, 100-V, 200-mA, 225-mW	SOD-123	MMSD914T1	On Semi
1	D8	BAT54AWT1	Diode, Dual Schottky, 200-mA, 30-V	SOT323	BAT54AWT1	On Semi
3	J1, J2, J5	8600-0-05-xx-00-00-03-0	Header, Single pin	0.072 x 1	8600-0-05-01-00-00-03-0	Mill-Max
2	J3, J4	8952-0-05-xx-00-00-03-0	Header, Single pin	0.125 x 1	8952-0-05-01-00-00-03-0	Mill-Max
1	L1	2.4uH	Inductor, SMT	0.770 x 0.780 inch	PA1494.242ANL	Pulse
1	L2	1mH	Inductor, SMT, 0.1A, 14ohm	0.26x0.09 inch	DO1608C-105ML	Coilcraft
1	Q1	BCX5616TA	TRANSISTOR NPN 80V SOT-89	SOT-89	BCX5616TA	Diodes
4	Q2, Q3, Q8, Q10	CSD16401Q5A-R	MOSFET, NChan, 25V, 37A, 1.3milliOhm	QFN5X6mm	CSD16401Q5A-R	TI
1	Q4	IRF6216	MOSFET, P-ch, 150-V, 2.2-A, 240-milliOhms	SO8	IRF6216	International Rectifier
2	Q5, Q6	IRFH5015PBF	MOSFET, NChan, 150V, 30A, 31millohm	PWRPAK S0-8	IRFH5015PBF	
1	Q7	MMBT3904	Bipolar, NPN, 40-V, 200-mA	SOT23	MMBT3904LT1	On Semi
1	Q9	MMBT3906	Bipolar, PNP, 40-V, 200-mA	SOT23	MMBT3906LT1	On Semi
1	R1	1k	Resistor, Chip, 1/16W, x%	0805	Std	Std
1	R10	3.74k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R101	49.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R12	1.65k	Resistor, Chip, 1/16W, 1%	0603	Std	Std

PMP5997_REVC BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
2	R13, R100	7.5k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R14, R16	75k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R17	121k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R18, R22	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R19	49.9k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
4	R2, R5, R24, R30	DNP	Do Not Populate	0603	N/A	N/A
2	R25, R31	499k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R26	301	Resistor, Chip, 1/16W, 1%	0603	Std	Std
4	R3, R15, R27, R29	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R32	6.04k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R4	20	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R6, R7	0.05	Resistor, Chip, 1-W, 1%	2512	Std	Std
4	R8, R21, R23, R28	1k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
3	R9, R11, R20	100k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	T1	JA4309-AL	Transformer, Planar	20.57 x 23.37 mm	JA4309-AL	Coilcraft
1	TP1	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100	5000	Keystone
1	U1	TPS28225DRB	IC, High Frequency 4-Amp MOSFET Driver	QFN	TPS28225DRB	TI
1	U2	UCC2897APW	IC, Current-Mode Active Clamp PWM Controller	PW20	UCC2897APW	Texas Instruments
1	U3	ISO7220MD	IC, DUAL DIGITAL ISOLATORS	SO-8	ISO7220xD	TI
1	U4	TL331DBV	IC, COMPARATOR, DIFFERENTIAL, SINGLE	SOT_23_5 (DBV)	TL331DBV	TI
1	U5	TCMT1107	IC, Photocoupler, CTR = 80% - 160%	MF4	TCMT1107	Vishay
1	U6	TLV431ADBZ	IC, Low-Voltage Adjustable Shunt Regulator	SOT23-3	TLV431AIDBZ	TI

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated