



1 Photo

The photograph below shows the top view and bottom view of the PMP5123 Rev A demo board. The circuit is built on a PMP3804 Rev A PWB.



2 Efficiency

The efficiency data is shown in the tables and graph below.




Iout	Vout	Vin	Iin	Pout	Losses	Efficiency	Iout	Vout	Vin	Iin	Pout	Losses	Efficiency
0.000	12.13	8.00	0.381	0.00	3.048	0.0%	0.000	12.13	12.00	0.212	0.00	2.544	0.0%
1.000	12.13	8.00	1.908	12.13	3.134	79.5%	0.994	12.13	12.00	1.212	12.06	2.487	82.9%
2.002	12.12	8.00	3.467	24.26	3.472	87.5%	1.996	12.13	12.00	2.240	24.21	2.669	90.1%
3.002	12.12	8.00	5.04	36.38	3.936	90.2%	2.998	12.13	12.00	3.281	36.37	3.006	92.4%
4.001	12.12	8.00	6.65	48.49	4.708	91.2%	4.003	12.12	12.00	4.34	48.52	3.564	93.2%
5.00	12.12	8.01	8.29	60.61	5.791	91.3%	5.00	12.12	12.00	5.40	60.60	4.200	93.5%
6.00	12.12	7.99	9.97	72.76	6.904	91.3%	6.00	12.12	12.00	6.49	72.72	5.160	93.4%
7.00	12.12	8.01	11.64	84.84	8.396	91.0%	7.00	12.12	12.00	7.61	84.84	6.480	92.9%
Iout	Vout	Vin	Iin	Pout	Losses	Efficiency	Iout	Vout	Vin	Iin	Pout	Losses	Efficiency
0.000	12.13	24.01	0.131	0.00	3.145	0.0%	0.000	12.14	36.01	0.110	0.00	3.961	0.0%
1.008	12.13	23.99	0.641	12.23	3.151	79.5%	0.999	12.14	36.00	0.451	12.13	4.108	74.7%
2.002	12.13	23.99	1.151	24.28	3.328	87.9%	2.000	12.13	35.99	0.796	24.26	4.388	84.7%
2.998	12.13	23.93	1.672	36.37	3.645	90.9%	3.001	12.13	36.02	1.142	36.40	4.733	88.5%
4.002	12.13	23.99	2.194	48.54	4.090	92.2%	3.999	12.13	36.01	1.492	48.51	5.219	90.3%
5.00	12.13	24.00	2.726	60.65	4.774	92.7%	5.00	12.13	35.97	1.851	60.65	5.930	91.1%
6.00	12.13	24.00	3.267	72.80	5.604	92.9%	6.00	12.13	35.99	2.215	72.78	6.938	91.3%
6.99	12.12	24.00	3.813	84.72	6.793	92.6%	7.01	12.13	36.02	2.589	85.03	8.224	91.2%


3 Thermal Images

The thermal images below show a top view (left) and bottom view (right) of the board. The ambient temperature was 26°C with no forced air flow. The output was loaded with 7A.

3.1 12V Input





3.2 24V Input



4 Startup


The output voltage at startup is shown in the images below. The input was 12VDC. For the top image, the output was unloaded. For the bottom image, the output was loaded with 7A.






5 Output Ripple Voltage

The output ripple voltage during full load operation (7A load) is shown in the plot below. The input voltage was set to 12VDC.




6 Loop Response

The image below shows the loop response of the converter. The output was loaded with 7A. For the upper gain/phase plot, the input was set to 24V. For the lower gain/phase plot, the input was set to 12V.



7 Load Transients

The image below shows the response to a 3A to 6A load transient. The input voltage was set to 12VDC.
 Channel 1: Vout (ac coupled) 500mV/div
 Channel 4: Iout 2A/div





8 Switching Waveforms

The images below show the drain-to-source voltage waveforms on the switching MOSFETs. The output was loaded with 7A. For the top image, the input was set to 36V. For the bottom image, the input was set to 8V.

Channel 1: Q6 and Q7 Vds

Channel 2: Q11 and Q12 Vds

Channel 3: Q9 Vds



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated