



1 Photo

The photographs below show the top and bottom views of the PMP7451 Rev B demo board. The circuit is built on a PMP7451 Rev A PWB.



2 Efficiency



PMP7451 Rev B Test Results


Iout	Vout	Vin	Iin	Pout	Losses	Efficiency
0.000	12.02	36.0	0.123	0.00	4.428	0.0%
1.009	12.04	36.0	0.456	12.15	4.268	74.0%
2.000	12.04	36.0	0.788	24.08	4.288	84.9%
2.987	12.04	36.0	1.121	35.96	4.393	89.1%
4.003	12.05	36.0	1.470	48.24	4.684	91.1%
4.998	12.05	36.0	1.812	60.23	5.006	92.3%
5.998	12.06	36.0	2.161	72.34	5.460	93.0%
7.01	12.06	36.0	2.519	84.54	6.143	93.2%
8.00	12.06	36.0	2.873	96.48	6.948	93.3%
9.01	12.07	36.0	3.237	108.75	7.781	93.3%
10.00	12.07	36.0	3.599	120.70	8.864	93.2%

Iout	Vout	Vin	Iin	Pout	Losses	Efficiency
0.000	12.09	48.0	0.084	0.00	4.032	0.0%
1.007	12.09	48.0	0.337	12.17	4.001	75.3%
2.003	12.09	48.0	0.589	24.22	4.056	85.7%
2.996	12.08	48.0	0.842	36.19	4.224	89.5%
4.007	12.08	48.0	1.102	48.40	4.491	91.5%
5.002	12.08	48.0	1.360	60.42	4.856	92.6%
6.001	12.08	48.0	1.620	72.49	5.268	93.2%
7.00	12.08	48.0	1.883	84.56	5.824	93.6%
8.00	12.08	48.0	2.150	96.64	6.560	93.6%
9.01	12.08	48.0	2.420	108.84	7.319	93.7%
10.00	12.08	48.0	2.688	120.80	8.224	93.6%


Iout	Vout	Vin	Iin	Pout	Losses	Efficiency
0.000	12.10	75.0	0.055	0.00	4.125	0.0%
1.005	12.09	75.0	0.217	12.15	4.125	74.7%
1.992	12.09	75.0	0.383	24.08	4.642	83.8%
2.992	12.09	75.0	0.550	36.17	5.077	87.7%
4.010	12.09	75.0	0.719	48.48	5.444	89.9%
5.008	12.09	75.0	0.886	60.55	5.903	91.1%
5.992	12.09	75.0	1.052	72.44	6.457	91.8%
6.98	12.09	75.0	1.220	84.39	7.112	92.2%
8.01	12.09	75.0	1.395	96.84	7.784	92.6%
9.01	12.09	75.0	1.571	108.93	8.894	92.5%
10.00	12.09	75.0	1.743	120.90	9.825	92.5%

3 Thermal Images


The thermal images below show a top view (left) and bottom view (right) of the board. The ambient temperature was 25C with 100LFM of forced air flow. The input was 48VDC, and the output was loaded with 10A.




4 Startup – 36V Input, No Load




5 Startup – 75V Input, No Load



6 Startup – 36V Input, 2Ω Load




7 Startup – 75V Input, 2Ω Load




8 Output Ripple Voltage

The output ripple voltage is shown in the plots below. The output was loaded with 10A.


8.1 36V Input



8.2 48V Input




8.3 75V Input




9 Frequency Response

The frequency response of the feedback loop is shown below. For the gain/phase plot #1, the input was set to 36V. For the gain/phase plot #2, the input was set to 75V. The output was loaded with 10A.

9.1 Measured Across R23




9.2 Measured Across R17




10 Load Transients

The response to a load step from 5A to 10A is shown in the images below. Channel 1: Vout (ac coupled); Channel 4: Iout


10.1 36V Input



10.2 48V Input



10.3 75V Input




11 Input Under-Voltage Lock-Out

The turn-on and turn-off input voltages were measured and recorded below.

Turn-On	35.3 V
Turn-Off	34.8 V

12 Output Over-Voltage


An output over-voltage was induced by shorting the +Remote Sense pin (J5) to ground. The output voltage waveform was captured and is displayed below.



13 Switching Waveforms


For the images below show the output was loaded with 10A.

13.1 Primary FET (Q2) Vds – 75V Input




13.2 Q1 & Q6 Synchronous FETs – 36V Input

Channel 1 – Q1 Vds; Channel 2 – Q6 Vds



13.3 Q1 & Q6 Synchronous FETs – 75V Input

Channel 1 – Q1 Vds; Channel 2 – Q6 Vds



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2012, Texas Instruments Incorporated