

Filename: PMP5270_REVB_bom.xls						
Date: 01/12/2010						
		PMP5270_REVB BOM				
COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	C21	10pF	Capacitor, Ceramic, 16V, X7R, 10%	603	Std	Std
1	C23	1800pF	Capacitor, Ceramic, 50V, X7R, 10%	603	Std	Std
1	C22	0.01uF	Capacitor, Ceramic, 50V, X7R, 10%	603	Std	Std
4	C1, C2, C3, C4	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	603	Std	Std
1	C18	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	603	Std	Std
0	C17	DNP	Capacitor, Ceramic, 100V, C0G, 10%	603	Std	Std
1	C8	220pF	Capacitor, Ceramic, 100V, C0G, 10%	805	Std	Std
1	C5	1000pF	Capacitor, Ceramic, 100V, X7R, 10%	805	Std	Std
2	C6, C12	0.1uF	Capacitor, Ceramic, 100V, X7R, 10%	805	Std	Std
2	C15, C24	1uF	Capacitor, Ceramic, 25V, X7R, 10%	805	Std	Std
0	C20	DNP	Capacitor, Ceramic, 200V, C0G, 10%	805	Std	Std
2	C10, C11	2.2uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	Std	Std
2	C13, C16	10uF	Capacitor, Ceramic, 25V, X7R, 10%	1210	C3225X7R1E106K	TDK
2	C25, C26	DNP	Capacitor, Ceramic, 25V, X7R, 10%	1210	C3225X7R1E106K	TDK
1	C7	1000pF	Capacitor, Ceramic, 2kV, X7R 10%	1808	C4520X7R3D102K	TDK
1	C19	2200pF	Capacitor, Ceramic, 2KV, X7R, 20%	1812	C4532X7R3D222K	TDK
1	C14	68uF	Capacitor, Tantalum, 25V, 200 milliOhms, 20%	7343 (E)	TPSE686M025R200	AVX
1	C9	22uF	Capacitor, Aluminum, 100V, 20%	8x10.2mm	EEVFK2A220P	Panasonic
1	D1		Diode, TVS, 58-V, 1W	SMA	SMAJ58A	Diodes Inc.
0	D10	ALT	Diode, Schottky, 8.0-A,35-V,	TO-252AA	MBRD835L	On Semi
1	D11		Diode, Schottky, 3A, 60V	SMC	MBRS360T3	On Semi
2	D2, D3		Bridge Rectifier, 100V, 0.8A	MINI DIP4	HD01	Diodes, Inc
0	D4	DNP	Rectifier, Ultrafast Power, 200V 1A	SMA	MURA120T3	On Semi
2	D6, D9		Rectifier, Ultrafast Power, 200V 1A	SMA	MURA120T3	On Semi
1	D7		Diode, Switching, 150V, 200mA, 250mW,	SOD-123	BAV20W	Diodes, Inc
1	D8		Diode, Dual Ultra Fast, Series, 200-mA, 70-V	SOT23	BAV99	Fairchild
2	FB1, FB2		Bead, Ferrite, SMT, 600 Ohms, 2A	805	MPZ2012S601A	TDK
2	J1, J2		Connector, Jack, Modular, 8 POS	0.705 x 0.820	5520252-4	AMP
2	J3, J4		Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25 inch	ED555/2DS	OST
1	L1	3.3uH	Inductor, SMT, 1.4A, 80milliohm	4x4mm	LPS4018-332ML	Coilcraft
1	Q1		MOSFET, N-ch, 150V, 3.7A, 85milliOhms	SO8	Si4848DY	Vishay
2	R12, R24	0	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R13	4.7	Resistor, Chip, 1/16W, 5%	603	Std	Std
4	R1, R2, R3, R4	75	Resistor, Chip, 1/16W, 5%	603	Std	Std
1	R11	90.9	Resistor, Chip, 1/16W,1%	603	Std	Std
1	R19	100	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R22	1.5K	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R15	3.48K	Resistor, Chip, 1/16W,1%	603	Std	Std
1	R25	4.02K	Resistor, Chip, 1/16W,1%	603	Std	Std
2	R16, R17	10K	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R27	17.8K	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R21	20K	Resistor, Chip, 1/16W, 1%	603	Std	Std

1	R7	24.9K	Resistor, Chip, 1/16W,1%	603	Std	Std
1	R9	60.4K	Resistor, Chip, 1/16W,1%	603	Std	Std
2	R10, R23	100K	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R26	392K	Resistor, Chip, 1/16W, 1%	603	Std	Std
1	R8	20	Resistor, Chip, 1/10W, 5%	805	Std	Std
1	R6	24K	Resistor, Chip, 1/10W, 5%	805	Std	Std
1	R20	0.27	Resistor, Chip, 1/4W, 1%	1206	Std	Std
1	R5	47	Resistor, Chip, 1/4 watt, 5%	1206	Std	Std
1	R100	0	Resistor, Chip, 1/2W, 5%	2010	Std	Std
0	R18	DNP	Resistor, Chip, 1/2W, 5%	2010	Std	Std
1	T1		Xfmr, Center-tapped, Voice Over IP	0.500 x 0.370	H2019	Pulse
1	T2		Transformer, Flyback, 15V	0.677 x 0.865 inch	HA4137-AL	Coilcraft
1	T3	ALT	Transformer, Flyback ±10%	0.551 x 0.695 inch	PA1528NL	Pulse
2	TP1, TP2		Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	TP4		Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
1	U2		IC, Photocoupler, 3750VRMS, 80-160% CTR	MF4	TCMT1107	Vishay
1	U3		IC, Precision Adjustable Shunt Regulator	SOT23-5	TL431AIDBVR	TI
1	U1		IC, IEEE 802.3af Integrated Primary Side Controller with Enhar	TSSOP14	TPS23753APW	TI

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps