

Filename: PMP5236_REVA_bom.xls						
Date: 12/01/2009						
		PMP5236_REVA BOM				
COUNT	RefDes	Value	Description	Size	Part Number	Mfr
6	C19, C39, C50, C52, C54, C56	47pF	Capacitor, Ceramic, 50V, C0G, 10%	603	Std	Std
2	C24, C44	100pF	Capacitor, Ceramic, 50V, C0G, 10%	603	Std	Std
2	C18, C38	330pF	Capacitor, Ceramic, 100V, C0G, 10%	603	Std	Std
2	C1, C4	1000pF	Capacitor, Ceramic, 100V, X7R, 10%	603	Std	Std
2	C23, C43	0.01uF	Capacitor, Ceramic, 16V, X7R, 10%	603	Std	Std
4	C5, C6, C7, C8	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	603	Std	Std
2	C25, C45	0.033uF	Capacitor, Ceramic, 50V, X7R, 10%	603	Std	Std
2	C26, C46	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	603	Std	Std
4	C51, C53, C55, C57	1uF	Capacitor, Ceramic, 16V, X7R, 10%	603	Std	Std
6	C10, C14, C29, C30, C34, C49	0.1uF	Capacitor, Ceramic, 100V, X7R, 10%	805	Std	Std
4	C22, C28, C42, C48	1uF	Capacitor, Ceramic, 25V, X7R, 10%	805	Std	Std
2	C27, C47	2.2uF	Capacitor, Ceramic, 16V, X7R, 10%	805	Std	Std
4	C12, C13, C32, C33	2.2uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	C3225X7R2A225K	TDK
4	C15, C16, C35, C36	22uF	Capacitor, Ceramic, 16V, X5R, 20%	1210	Std	Std
3	C9, C20, C40	1000pF	Capacitor, Ceramic, 2KV, X7R, 10%	1812	C4532X7R3D102K	TDK
2	C21, C41	22uF	Capacitor, Aluminum, 16V, 20%	5x5.8mm	EEEFK1C220R	Panasonic
2	C17, C37	150uF	Capacitor, Aluminum, 16V, 20%	6.3x7.7mm	EEEFK1C151XP	Panasonic
2	C11, C31	47uF	Capacitor, Aluminum, 63V, ±20%	8x10.2mm	EEEFK1J470P	Panasonic
8	D1, D2, D4, D5, D6, D7, D9, D10		Diode, Schottky, 1A, 100V	SMA	B1100	Diodes, Inc
2	D11, D16		Diode, Rectifier, 1A, 200V	SMA	MURA120	On Semi
4	D12, D14, D17, D19		Diode, Switching, 100-V, 200-mA, 225-mW	SOD-123	MMSD914T1	On Semi
2	D13, D18		Diode, Schottky, 7A, 60V	Power DI-5	PDS760	Diodes
2	D15, D20		Diode, Dual Schottky, 200mA, 30V	SOT23	BAT54S	Diodes, Inc
2	D3, D8		Diode, SMT TVS 400W, 4.3-A, 58-V	SMA	SMAJ58A	Diodes
4	FB1, FB2, FB3, FB4		Bead, Ferrite, SMT, 150 Ohms, 1.5A	805	MMZ2012R150A	TDK
2	J1, J2		Connector, Jack, Modular, 8 POS	0.705 x 0.820 inch	520252-4	AMP
6	J3, J4, J5, J6, J8, J9		Header, Male 2-pin, 100mil spacing,	0.100 inch x 2	PEC02SAAN	Sullins
1	J7		Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	
2	L1, L3	3.3uH	Inductor, SMT, 1.53A, 32milliohm	5.1x5.1mm	MSS5131-332MX	Coilcraft
2	L2, L4	0.33uH	Inductor, SMT, 3A, 25 milliohm	3.9x3.9mm	LPS4012-331ML	Coilcraft
2	Q1, Q3		MOSFET, N-ch, 150V, 4.9A, 47 milliohm	SO8	FDS2572	Fairchild
2	Q2, Q4		Bipolar, PNP, 40V, 200mA, 225mW	SOT23	MMBT3906LT1	On Semi

4	R15, R21, R38, R44	0	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R55, R62	15	Resistor, Chip, 1/16W, 5%	603	Std	Std
2	R10, R33	20	Resistor, Chip, 1/16W, 5%	603	Std	Std
2	R29, R52	63.4	Resistor, Chip, 1/16W, 1%	603	Std	Std
4	R5, R6, R7, R8	75	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R19, R42	100	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R60, R67	590	Resistor, Chip, 1/16W, 1%	603	Std	Std
6	R14, R37, R56, R58, R63, R65	1K	Resistor, Chip, 1/16W, 1%	603	Std	Std
4	R18, R20, R41, R43	2K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R28, R51	2.61K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R17, R40	3.01K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R31, R53	4.99K	Resistor, Chip, 1/16W, 1%	603	Std	Std
6	R16, R22, R23, R39, R45, R46	10K	Resistor, Chip, 1/16W, 1%	603	Std	Std
6	R24, R27, R30, R47, R50, R68	24.9K	Resistor, Chip, 1/16W, 1%	603	Std	Std
4	R57, R59, R64, R66	49.9K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R26, R49	69.8K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R25, R48	75K	Resistor, Chip, 1/16W, 1%	603	Std	Std
2	R12, R35	20	Resistor, Chip, 1/10W, 5%	805		std
4	R1, R2, R3, R4	0	Resistor, Chip, 1/4W, 5%	1206	Std	Std
2	R54, R61	0.025	Resistor, Chip, 1/4W, 1%	1206	Std	Std
2	R13, R36	0.25	Resistor, Chip, 1/2W, 1%	2010	Std	Std
2	R11, R34	24	Resistor, Chip, 1/2W, 5%	2010	Std	Std
2	R9, R32	39K	Resistor, Chip, 1W, 5%	2512	Std	Std
2	T1, T2		Transformer,	S0 14 Wide	ETH1-230LD	Coilcraft
2	T3, T4		Transformer, Flyback	0.810 X 1.181 inch	JA4387-AL	Coilcraft
1	TP1		Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
2	TP2, TP3		Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
2	U2, U6		IC, Photocoupler, 80-160% CTR	MF4	TCMT1107	Vishay
2	U4, U8		Photocoupler, 300-600% CTR, 3.75KV Isolation	MF4	PC357N4TJ00F	Sharp
2	U3, U7		IC, Shunt Regulator, 2.5V ref, 36V, 100mA, 1%	SOT23-5	TL431ACDBVR	Texas Instruments
2	U9, U10		IC, Load-Share Controller	MSOP-8	UCC29002DGK	Texas Instruments
2	U1, U5		IC, IEEE 802.3at PoE Interface/Isolated Converter Controller	PWP20	TPS23754PWP	Texas Instruments

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps