

Change in menu Project

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
IPCB	1		Printed Circuit Board		XX###	Any	-	-
C1	1	470pF	CAP, CERM, 470pF, 100V, +/-5%, COG/NP0, 0805	0805	GRM2165C2A471JA01D	MuRata	-	-
C3, C4	2	3300uF	CAP, AL, 3300uF, 16V, +/-20%, 0.035 ohm, SMD	SMT Radial J16	EEV-FK1C332M	Panasonic		
C5, C6, C8	3	1uF	CAP, CERM, 1uF, 100V, +/-20%, C Series, 1206	1206	C3216X7R2A105M	TDK	-	-
C7	1	100uF	CAP, AL, 100uF, 100V, +/-20%, 0.17 ohm, SMD	SMT Radial J16	EEV-FK2A101M	Panasonic		
C9	1	0.1uF	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0603	0603	GRM188R72A104KA35D	MuRata	-	-
C10, C12, C13	3	100pF	CAP, CERM, 100pF, 50V, +/-5%, COG/NP0, 0603	0603	GRM1885C1H101JA01D	MuRata	-	-
C11	1	4.7uF	CAP CER 4.7UF 10V 10% X6S 0603	0603 (1608 Metric)	C1608X6S1A475K	TDK Corporation	-	-
C14	1	0.047uF	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0603	0603	GRM188R71E473KA01D	MuRata	-	-
C15	1	0.47uF	CAP, CERM, 0.47uF, 100V, +/-10%, X7R, 0805	0805	GRM21BR72A474KA73L	MuRata		
C16	1	1uF	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	0603	C1608X7R1E105K080A	TDK		
C17	1	0.01uF	CAP, CERM, 0.01uF, 100V, +/-5%, X7R, 0603	0603	06031C103JAT2A	AVX		
C18	1	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603	06035C104KAT2A	AVX		
Cx1	1	1200uF	CAP, Al Electrolytic, 1200uF, 25V, +/-20%, 0.029Ohm ESR, TH		25ME1200AX	SUNCON	-	-
Cx2, Cx3, Cx4, Cx5	4	22uF	CAP, CERM, 22uF, 25V, 10%, 1206	1206	GRM31CR61E226KE15L	Murata Electronics	-	-
D2	1	0.57V	DIODE SCHOTTKY 1A 100V SOD-123FL	SOD-123FL	MBR1H100SFT3G	On Semiconductor	-	-
FID1, FID2, FID3	3		Fiducial mark. There is nothing to buy or mount.	Fiducial	N/A	N/A		
H1, H2, H3, H4	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw	NY PMS 440 0025 PH	B&F Fastener Supply	-	-
H5, H6, H7, H8	4		Standoff, Hex, 0.5"L #4-40 Nylon	Standoff	1902C	Keystone	-	-
L1	1	1.5uH	Inductor, Shielded E Core, Ferrite, 1.5uH, 30A, 0.0015 ohm, SMD	SER29xx	SER2915L-152KL	Coilcraft		
LBL1	1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W	THT-14-423-10	Brady	-	-
Q1	1	40V	MOSFET, N-CH, 40V, 100A, PG-TDSON-8	PG-TDSON-8	BSC030N04NS G	Infineon Technologies		None
Q2, Q3	2	60V	MOSFET, N-CH, 60V, 100A, PG-TDSON-8	PG-TDSON-8	BSC028N06LS3 G	Infineon Technologies		None
R1	1	7.5	RESISTOR 7.5 OHM 3/4W 5% 2010	2010	ERJ-12ZYJ7R5U	Panasonic	-	-
R2	1	0.001	RES, 0.001 ohm, 1%, 1W, 2512	2512	WSL25121L000FEA	Vishay/Dale	-	-
R3, R4	2	102	RES, 102 ohm, 1%, 0.1W, 0603	0603	CRCW0603102RFKEA	Vishay-Dale		
R5, R6, R8, R12, R21	5	0	RES, 0 ohm, 5%, 0.1W, 0603	0603	ERJ-3GEY0R00V	Panasonic	-	-
R10	1	26.1k	RES, 26.1k ohm, 1%, 0.1W, 0603	0603	CRCW060326K1FKEA	Vishay-Dale		
R11	1	3.3	RES, 3.3 ohm, 5%, 0.1W, 0603	0603	CRCW06033R30JNEA	Vishay-Dale	-	-
R13	1	7.87k	RES, 7.87k ohm, 1%, 0.1W, 0603	0603	CRCW06037K87FKEA	Vishay-Dale		
R14	1	51.1k	RES, 51.1k ohm, 1%, 0.1W, 0603	0603	CRCW060351K1FKEA	Vishay-Dale		
R16	1	40.2k	RES, 40.2k ohm, 1%, 0.1W, 0603	0603	CRCW060340K2FKEA	Vishay-Dale	-	-
R17	1	9.76k	RES, 9.76k ohm, 1%, 0.1W, 0603	0603	CRCW06039K76FKEA	Vishay-Dale		
R18	1	9.31k	RES, 9.31k ohm, 1%, 0.1W, 0603	0603	CRCW06039K31FKEA	Vishay-Dale		
R19	1	84.5k	RES, 84.5k ohm, 1%, 0.1W, 0603	0603	CRCW060384K5FKEA	Vishay-Dale	-	-
R20	1	3.48	RES, 3.48 ohm, 1%, 0.1W, 0603	0603	CRCW06033R48FKEA	Vishay-Dale	Equivalent	Any
TP1, TP2, TP3, TP4	4		Standard Banana Jack, Uninsulated, 8.9mm	Keystone575-8	575-8	Keystone	Equivalent	Any
TP5, TP7	2	Red	Test Point, TH, Multipurpose, Red	Keystone5010	5010	Keystone	Equivalent	Any
TP6, TP8, TP10	3	Black	Test Point, TH, Multipurpose, Black	Keystone5011	5011	Keystone	Equivalent, -, -	Any, -, -
TP9, TP11	2	White	Test Point, TH, Miniature, White	Keystone5002	5002	Keystone	-	-
TP12	1	White	Test Point, TH, Multipurpose, White	Keystone5012	5012	Keystone	Equivalent	Any
U1	1			eg: 0603, used in PnP report	LM5122MH	TI	-	-
C2	0	3300uF	CAP, AL, 3300uF, 16V, +/-20%, 0.035 ohm, SMD	SMT Radial J16	EEV-FK1C332M	Panasonic		
D1	0	0.77V	Diode, Schottky, 100V, 1A, PowerDI123	PowerDI123	DFLS1100-7	Diodes Inc.	-	-
R7	0	158k	RES, 158k ohm, 1%, 0.1W, 0603	0603	CRCW0603158KFKEA	Vishay-Dale	-	-
R9	0	DNP	RES, 3.3 ohm, 5%, 0.1W, 0603	0603	CRCW06033R30JNEA	Vishay-Dale	-	-
R15	0	DNP	RES, 0 ohm, 5%, 0.1W, 0603	0603	ERJ-3GEY0R00V	Panasonic	-	-

Notes:
Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.