

Filename: PMP2807_A_bom.xls

Date: 07/11/2007

PMP2807_A BOM

COUNT	RefDes	DESCRIPTION	SIZE	MFR	Part Number	Value
1	C1	Capacitor, Ceramic, 50V, C0G, 5%	0603	TDK	C1608C0G1H101J	100pF
1	C10	Capacitor, Aluminum, 6.3-V, 20%, FK Series	0.217 x 0.169	Panasonic	EEVFK0J101P	100uF
1	C11	Capacitor, Ceramic, 6.3VV, X5R	1210	Std	Std	22uF
1	C12	Capacitor, Ceramic, 50V, X7R, 10%	0603	TDK	C1608X7R1H392K	3900pF
1	C13	Capacitor, Ceramic, 0.47-uF, 16-V, X7R, 10%	0805	Panasonic	ECJ-2YB1C474K	0.47uF
2	C14, C15	Capacitor, Ceramic, 10-uF, 25-V, X5R, 20%	1206	Panasonic	ECJ-3YB1E106M	10uF
1	C16	Capacitor, Ceramic, 10-uF, 6.3-V, X5R, 20%	0805	Panasonic	ECJ-2FB0J106M	10uF
1	C17	Capacitor, Ceramic, 6.3V, X5R	1210	std	Std	47uF
1	C18	Capacitor, Ceramic, 0.01uF, 16-V, X7R, 10%	0603	Std	Std	0.01uF
2	C19, C22	Capacitor, Ceramic, 10-uF, 16-V, X7R	1206	Std	Std	10uF
2	C2, C3	Capacitor, Ceramic, 50-V, X5R, 20%	1210	TDK	C3225X5R1H335M	3.3uF
2	C20, C23	Capacitor, Ceramic, 1-uF, 16-V, X7R	0603	std	std	1uF
1	C21	Capacitor, Aluminum, 6.3V, ±20%, 0.36ohms	.260 x 0.276 inc	Panasonic	EEVFK0J101P	100uF
1	C24	Capacitor, Aluminum, 6.3V, 20%, 80mohms	0.457 x 0.406	Panasonic	EEVFK0J152P	1500uF
2	C25, C28	Capacitor, Ceramic, 0.1-uF, 50-V, X7R, 15%	0603	TDK	Std	0.1uF
2	C26, C29	Capacitor, Ceramic, 16V, X7R	0805	std	std	2.2uF
2	C27, C30	Capacitor, Ceramic, 0.01uF, 50-V, X7R, 15%	0603	TDK	Std	0.01uF
1	C31	Capacitor, Ceramic, 16-V, X7R	1206	Std	Std	open
1	C4	Capacitor, Aluminum, SM, FK series	10x12mm	Panasonic	EEVFK1H221P	220uF
1	C5	Capacitor, Ceramic, 50V, X7R, 10%	0603	TDK	C1608X7R1H153K	0.015uF
1	C6	Capacitor, Ceramic, 50V, X7R, 10%	0603	TDK	C1608X7R1H681K	680pF
1	C7	Capacitor, Ceramic, 16V, X7R, 10%	0603	TDK	C1608X7R1C474M	0.47uF
1	C8	Capacitor, Ceramic, 50V, X7R, 10%	0603	TDK	C1608X7R1H104K	0.1uF
1	C9	Capacitor, Ceramic, 50V, X7R, 10%	0603	TDK	C1608X7R1H151K	150pF
1	D1	Diode, Schottky, 3-A, 60-V	SMC	On Semi	MBRS360T3	MBRS360
2	D2, D4	Diode, LED, Green, 2.1-V, 20-mA, 6-mcd	0603	Liteon	160-1183-1-ND	Green
1	D3	Diode, LED, Red, 1.8-V, 20-mA, 20-mcd	0603	Liteon	160-1181-1-ND	Red
2	D5, D6	Diode, Schottky, 1000-mA, 20-V	SOD123	On Semi	MBR120ESFT1	MBR120ESFT1
5	J1, J2, J3, J5, J6	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	OST	D120/2DS	D120/2DS
1	J4	Terminal Block, 3-pin, 15-A, 5.1mm	0.60 x 0.35 inch	OST	D120/3DS	D120/3DS
2	J7, J8	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35		ED1609	ED1609-ND
1	L1	Inductor, SMT, 3.23A, 60milliohm	0.492 sq"	Coiltronics	DR127-330-R	33uH
1	L2	Inductor, SMT, 0.9A, 230milliohm	0.26x0.09 inch	Coilcraft	DO1608C-153	15uHy
1	L3	Inductor, SMT, 2A, 80milliohm	0.26x0.09 inch	Coilcraft	DO1608C-332	3.3uHy

1	Q1	Transistor, MOSFET, Pch, -3A, -60V, 105 milliohm	SuperSOT-6	Fairchild	FDC5614P	FDC5614P
2	Q2, Q3	MOSFET, P-ch, -30-V, 1.95-A, 155-milliOhms	SOT23	On Semi	NTR4502P	NTR4502P
1	R1	Resistor, Chip, 1/16W, 1%	0603	Std	Std	69.8k
3	R10, R11, R12	Resistor, Chip, 1.5K-Ohms, 1/16-W, 1%	0603	Std	Std	1.5K
3	R13, R15, R20	Resistor, Chip, 100K-Ohms, 1/16-W, 1%	0603	Std	Std	100k
1	R14	Resistor, Chip, 0-Ohms, 1/16-W, 1%	0603	Std	Std	0
1	R16	Resistor, Chip, 10k-Ohms, 1/16-W, 1%	0603	Std	Std	10k
1	R17	Resistor, Chip, 1/10W, 1%	0805	Std	Std	825
1	R18	Resistor, Chip, 30.1k-Ohms, 1/16-W, 1%	0603	Std	Std	30.1k
1	R19	Resistor, Chip, 1/16-W, 1%	0603	Std	Std	32.4k
1	R2	Resistor, Chip, 1/10W, 5%	0805	Std	Std	0.01
1	R21	Resistor, Chip, 1/10W, yy%	0805	Std	Std	0.27
2	R22, R28	Resistor, Chip, 10K, 1%, 0603	0603	Std	Std	10K
4	R23, R24, R29, R30	Resistor, Chip, 0-Ohms, 0603	0603	Std	Std	0
1	R25	Resistor, Chip, 60.4K, 1%, 0603	0603	Std	Std	60.4K
2	R26, R32	Resistor, Chip, 121k, 1%, 0603	0603	Std	Std	121k
1	R27	Resistor, Chip, 1/8W, yy%	1206	Std	Std	0.05
1	R3	Resistor, Chip, 1/16W, 1%	0603	Std	Std	1k
1	R31	Resistor, Chip, 1%, 0603	0603	Std	Std	210k
1	R4	Resistor, Chip, 1/16W, 1%	0603	Std	Std	0
1	R5	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5.76k
3	R6, R33, R34	Resistor, Chip, 1/16W, 1%	0603	Std	Std	10k
1	R7	Resistor, Chip, 1/16W, 1%	0603	Std	Std	4.22k
1	R8	Resistor, Chip, 1/16W, 1%	0603	Std	Std	1.62k
1	R9	Resistor, Chip, 1/16W, 1%	0603	Std	Std	49.9
15	TP1, TP5, TP7, TP8, TP10, TP12, TP13, TP18, TP20, TP23, TP25, TP28, TP30, TP31, TP33	Test Point, Red, Thru Hole Color Keyed	.100 x 0.100 inc	Keystone	5000	5000
11	TP2, TP3, TP6, TP11, TP17, TP21, TP22, TP26, TP27, TP29, TP32	Test Point, Black, Thru Hole Color Keyed	.100 x 0.100 inc	Keystone	5001	5001
3	TP4, TP19, TP24	Test Point, SMT	.105 x 0.040 inc	Keystone	5015	5015

	TP9, TP14, TP15,					
4	TP16	Test Point, 0.032 Hole		None	Void	
1	U1	IC, Low Cost Sync Buck Controller	SO-8	Texas Instruments	TPS40200D	TPS40200D
1	U2	IC, Single-IC Charge and System Power Path Management	QFN	TI	bq24070RHL	BQ24070RHL
2	U3, U4	IC, Step-Down Controller	SOT23-6	TI	TPS64203DBV	TPS64203DBV
1	U5	IC, UltraLow-Noise, High PSRR, Fast RF 200 mA, LDO Regulat	SOT23-6	TI	TPS73018DBVR	TPS73018DBVR
1	U6	IC, UltraLow-Noise, High PSRR, Fast RF 200 mA, LDO Regulat	SOT23-6	TI	TPS73033DBVR	TPS73033DBVR

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
 2. These assemblies must be clean and free from flux and all contaminants.
Use of no clean flux is not acceptable.
 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
 4. Ref designators marked with an asterisk ('**') cannot be substituted.
All other components can be substituted with equivalent MFG's components.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated