

1020	GBU8K	Vishy	1	BD100
1030	MFET N BSS127	Infenon	1	Q119
1040	UCC28051	TI	1	IC100
1050	ZD15V/1W	PANJIT	3	ZD110, ZD202, ZD952
1060	20V/600A	Infenon	1	Q101
1070	DIO 600V/8A	PAC	1	D100
1080	UCC28610	TI	1	IC500
1090	1N4148WS/SMD	PANJIT	23	D910, D916, D502, D202, D203, D204, D205, D206, D320, D321, D322, D323, D348, D349, D350, D351, D352, D353, D354, D355, D356, D370, D371
1100	2A/800V	Infenon	1	Q500
1110	800V/2A	Vishy	1	D500
1120	200V/2A	PANJIT	9	D503, D360, D361, D362, D363, D364, D365, D366, D367
1130	PHOTO	NEC	3	PC500, PC200, PC920
1140	VFT2060	Vishy/PANJIT	3	D555, D262, D272
1160	Si4840	Vishy	1	Q330
1180	BJT/4403		6	Q332, Q355, Q954, Q950, Q905, Q912
1190	BJT/ 4401		5	Q331, Q358, Q953, Q900, Q914
1200	UCC24610		1	IC310
1210	TL431		3	IC560, IC251, IC252
1220	UCC25600	TI	1	IC200
1230	600v/4A	PAC	4	Q300, Q301, Q200, Q201
1270	MPS651	PANJIT	1	Q952
1280	LM358	TI	1	IC920
2010	SCK15075		2	TH001, TH002
2020	330k/0805		8	R001, R002, R003, R004, R380, R381, R382, R383
2030	499K/0805		9	R100, R101, R102, R103, R113, R114, R115, R116, R117
2040	100/0805		3	R119, R109, R215
2045	100/2W		1	R952
2060	68.1K/0805		1	R105
2065	22/0805		1	R325
2070	47/0805		4	R110, R106, R210, R321
2080	10K/0805		13	R104, R107, R202, R205, R252, R302, R305, R362, R950, R951, R912, R914, R901
2100	0.2/2W		1	R108
2110	3.32K/0805		5	R111, R563, R255, R317, R907
2120	16.2K/0805		1	R118
2130	2.2M/0805		4	R501, R502, R503, R504
2140	75K/0805		2	R514, R511
2150	110K/0805		1	R206
2150	33.2K/0805		2	R913, R915
2155	37.4K/0805		1	R513
2160	30.1K/0805		2	R512, R313
2160	6.19K/0805		1	R314
2165	36.5K/0805		1	R254
2180	10/0805		11	R505, R506, R515, R516, R201, R204, R208, R209, R301, R304, R332
2190	124K/0805		1	R510
2200	150K/2W		1	R500
2270	4.99K/0805		3	R564, R253, R920
2275	48.7K/0805		1	R315
2290	4.75K/0805		4	R562, R953, R954, R955
2300	1K/0805		6	R561, R251, R256, R331, R333, R906
2302	11.8K/0805		1	R316
2310	2K/0805		1	R250
2310	510/0805		2	R560, R918
2320	7.5K/0805		2	R211, R370
2340	1M/2W		1	R213
2350	15K/0805		1	R319
2350	56K/0805		1	R207
2360	2.74K/0805		1	R212
2370	470/0805		1	R230
2375	470K/0805		2	R216, R352
2400	6.81K/0805		1	R910
2420	22.1K/0805		7	R320, R355, R356, R357, R358, R911, R916
2425	24.9K/0805		1	R919
2430	2/2W	SungTa	1	R330
2440	7.5M/0805		1	R353

2460	100K/0805		
2570	180K/0805		
2570	5.1M/0805		
2580	1M/0805		
2580	240K/0805		
3010	470pF/Y-cap		
3020	0.47uF/X-cap	PAC	
3030	1uF/450V	PAC	
3050	2.2uF/0805		
3070	1000pF/1KV RSB	PAC	
3080	1000pF/0805		
3080	39uF/450V 10*50	NDB	
3082	100pF/0805		
3085	470pF/0805		
3090	0.047uF/0805		
3110	100uF/50V	NDB	
3130	470uF/25V 8*20	NDB	
3140	1000uF/10V 8*20	NDB	
3145	470uF/10V 8*10	NDB	
3150	1uF/0805		
3160	0.01uF/0805		
3162	220pF/0805		
3163	3300pF/0805		
3170	0.47uF/0805		
3180	0.022uF/0805		
3190	0.015uF/1KV R75	PAC	
3195	0.012uF/1KV R75	PAC	
3200	0.1uF/0805		
3210	0.047uF/100V R82	PAC	
3220	27uF/100V 8*15	NDB	
3235	150pF/0805		
3385	2200pF/0805		
4010	common choke	Transmore	
4030	PQ3811-4P	Transmore	
4050	DR8*10 1mm 6uH	Transmore	
4060	EPC13-1	Transmore	
4060	EPC13-2	Transmore	
4060	EPC13-3	Transmore	
4070	EEL21.2	Transmore	
4070	EPC3028	Transmore	
4080	EE16	Transmore	
6010	FUSE 250V/3.15A		
6030	AC connector		
6040	Connector 2.54 6p		
7000	HS	WD	
7050	PCB		

4	R900, R902, R904, R905
1	R360
1	R350
1	R351
1	R361
4	C010, C001, C123, C125
2	C001, C002
1	C100
2	C111, C207
6	C120, C500, C501, C200, C202, C300
9	C118, C109, C511, C208, C256, C356, C914, C915, C910
3	C121, C122, C123
2	C351, C354
1	C312
2	C505, C560
1	C502
2	C260, C261
4	C551, C553, C270, C271
1	C554
8	C110, C503, C564, C205, C230, C320, C325, C310
4	C255, C901, C900, C905
1	C316
1	C317
2	C561, C204
1	C206
1	C201
1	C201
5	C311, C370, C352, C953, C912
2	C362, C367
4	C360, C361, C365, C366
1	C333
1	C319
2	L001, L002
1	L100
1	L550
1	T210
1	T310
1	T320
2	T300, T301
1	T200
1	T500
1	F2
1	CN2
1	OUTPUT
2	Q101, D100
1	PCB

s	20V/600A	Infenon	1 Q101
s	2A/800V	Infenon	1 Q500
s	MFET N BSS127	Infenon	1 Q119
s	1000uF/10V 8*20	NDB	4 C551, C553, C270, C271
s	100uF/50V	NDB	1 C502
s	27uF/100V 8*15	NDB	4 C360, C361, C365, C366
s	39uF/450V 10*50	NDB	3 C121, C122, C123
s	470uF/10V 8*10	NDB	1 C554
s	470uF/25V 8*20	NDB	2 C260, C261
OK	PHOTO	NEC	3 PC500, PC200, PC920
s	0.012uF/1KV R75	PAC	1 C201
s	0.015uF/1KV R75	PAC	1 C301
s	0.047uF/100V R82	PAC	2 C362, C367
s	1000pF/1KV RSB	PAC	6 C120, C500, C501, C200, C202, C300
s	1uF/450V	PAC	1 C100
s	600v/4A	PAC	4 Q300, Q301, Q200, Q201
s	DIO 600V/8A	PAC	1 D100
OK	200V/2A	PANJIT	9 D503, D360, D361, D362, D363, D364, D365, D366, D367
s	MPS651	SungTa	1 Q952
OK	ZD15V/1W	PANJIT	3 ZD110, ZD202, ZD952
s	2/2W	SungTa	1 R330
OK	TL103WA	TI	1 IC920
OK	UCC25600	TI	1 IC200
OK	UCC28051	TI	1 IC100
OK	UCC28610	TI	1 IC500
	common choke	Transmore	2 L001, L002
	PQ3811-4P	Transmore	1 L100
	DR8*10 1mm 6uH	Transmore	1 L550
	EE16	Transmore	1 T500
	EPC13	Transmore	1 T210
	EPC3028	Transmore	1 T200
	EPC13	Transmore	1 T310
	Ring	Transmore	1 T320
	EEL21.2	Transmore	2 T300, T301
	GBU8K	Vishy	1 BD100
	Si4840	Vishy	1 Q330
	MBR2045F	Vishy	3 D555, D262, D272
s	HS	WD	2 Q101, D100

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated