

Filename: PMP8408_RevC_bom.xls						
Date: 12/20/2012						
		PMP8408 REV C BOM				
COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	C35	68pF	Capacitor, Ceramic, 50V, C0G, 10%	603	STD	Std
4	C5, C6, C7, C8	330pF	Capacitor, Ceramic, 50V, C0G, 10%	603	STD	Std
2	C20, C30	1000pF	Capacitor, Ceramic, 50V, C0G, 10%	603	STD	Std
2	C4, C9	1000pF	Capacitor, Ceramic, 100V, X7R, 10%	603	STD	Std
1	C100	1500pF	Capacitor, Ceramic, 50V, X7R, 10%	603	STD	Std
2	C1, C2	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	603	STD	Std
5	C13, C19, C29, C36, C38	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	603	STD	Std
1	C34	0.15uF	Capacitor, Ceramic, 50V, X7R, 10%	603	STD	Std
2	C32, C33	0.47uF	Capacitor, Ceramic, 16V, X7R, 10%	603	STD	Std
4	C12, C18, C28, C39	1uF	Capacitor, Ceramic, X7R, 16V, 10%	603	STD	Std
0	C20	DNP	Capacitor, Ceramic, 50V, C0G, 10%	603	STD	Std
2	C24, C40	0.1uF	Capacitor, Ceramic, 100V, X7R, 10%	805	STD	Std
1	C37	1uF	Capacitor, Ceramic, 25V, X7R, 10%	805	STD	Std
2	C10, C11	3.3uF	Capacitor, Ceramic, 16V, X7R, 10%	805	STD	Std
3	C3, C14, C15	1000pF	Capacitor, Ceramic, 2KV, X7R, 10%	1210	STD	Std
2	C22, C23	2.2uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	C3225X7R2A225K	TDK
4	C16, C17, C26, C27	100uF	Capacitor, Ceramic, 6.3V, 20%	1210	C3225X5R0J107M	TDK
1	C25	DNP	Capacitor, Ceramic, 6.3V, 20%	1210	C3225X5R0J107M	TDK
1	C31	22uF	Capacitor, Aluminum, 25V, 20%	5x5.8mm	EEEFK1E220R	Panasonic
1	C21	22uF	Capacitor, Aluminum, 100V, 20%	8x10.2mm	EEEFK2A220P	Panasonic
4	D1, D2, D3, D4		Diode, Schottky, 1A, 100V	SMA	B1100	Diodes, Inc
0	Alternate D1, D2, D3, D4		Diode, Schottky, 1A, 100V	SMA	S100	WTE
1	D13		Diode, Switching, 100V, 200mA, 400mW,	SOD-123	MMSD4148	On Semi
1	D15		Diode, Dual Schottky, 200-mA, 30-V	SOT23	BAT54S	Zetex
1	D16		Diode, SMT TVS 400W, 4.3-A, 58-V	SMA	SMAJ58A	Diodes
2	D6, D10		Rectifier, Superfast Power, 200V 1A	SMA	ES1D	Diodes, Inc
1	D7		Diode, Schottky, 1A, 40V	SMA	B140	Diodes, Inc
1	D8	10V	Diode, Zener, 10V, 250mW	SOT-23	BZX84C10LT1	On Semi
4	D9, D11, D12, D14		Diode, Schottky, 0.5A, 30V	SOD-123	MBR0530	On Semi
4	FB1, FB2, FB3, FB4	15	Bead, Ferrite, SMT, 15 Ohms, 1.5A	805	MMZ2012R150A	TDK
2	J1, J3		Connector, Jack, Modular, 8 POS	0.705 x 0.820	520252	AMP
4	J6, J7, J8, J9		Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED555/2DS	OST
0	L1	DNP	Inductor, SMT, 0.79A, 300milliohm	3.5x3.7mm	VLF4012AT-100MR79	TDK

4	Q1, Q2, Q3, Q4		Transistor, NFET, 100V, 1.5A, 250 milliohm	SOT-23	Si2328DS	Vishay
0	Alternate, Q1, Q2, Q3, Q4		Transistor, NFET, 100V, 1.7A, 240 milliohm	SOT-23	AP2330GN-HF	APEC
2	Q6, Q9		Transistor, MOSFET, N-Chan, 30V, 65A, 11.8milliOhm	QFN-8 Power	CSD17507Q5A	TI
2	Q7, Q10		Transistor, PNP, 40V, 200mA, 225mW	SOT23	MMBT3906LT1G	On Semi
1	Q8		Trans, Nch, 150V, 2.3A, 144milliohm	SuperSOT-6	FDC86244	Fairchild
2	R16, R30	0	Resistor, Chip, 1/16W, 5%	603	STD	Std
3	R20, R21, R25	10	Resistor, Chip, 1/16W, 5%	603	STD	Std
1	R17	49.9	Resistor, Chip, 1/16W, 1%	603	STD	Std
2	R3, R4	75	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R44	90.9	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R37	237	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R40	402	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R22	825	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R41	1K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R38	2K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R50	3.01K	Resistor, Chip, 1/16W, 1%	603	STD	Std
3	R31, R34, R39	10K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R42	68.1K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R43	24.9K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R47	5.90K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R48	20K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R46	69.8K	Resistor, Chip, 1/16W, 1%	603	STD	Std
1	R49	100K	Resistor, Chip, 1/16W, 1%	603	STD	Std
4	R11, R12, R13, R14	150K	Resistor, Chip, 1/16W, 1%	603	STD	Std
4	R7, R8, R9, R10	499K	Resistor, Chip, 1/16W, 1%	603	STD	Std
2	R23, R24	1	Resistor, Chip, 1/10W, 1%	805	STD	Std
2	R19, R26	10	Resistor, Chip, 1/10W, 5%	805	STD	Std
1	R27	20	Resistor, Chip, 1/10W, 5%	805	STD	Std
1	R18	39K	Resistor, Chip, 1/10W, 5%	805	STD	Std
1	T1		XFMR, 1000 Base-T, Ratio 1:1	0.500 x 0.370 inch	H2019	Pulse
1	T2		Transformer, Flyback	13.5x17.75 mm	NA6069-AL	Coilcraft
0	Alternate T2		Transformer, Flyback	13.5x17.75 mm	LDT0571-50	LinkCom
1	T3		Transformer, Gate Drive, 1mH	9.7x7.8mm	LTC0266-50	LinkCom
1	U5		IC, Photocoupler, 80-160% CTR	SOP-4	LTV817AS	Lite-on
1	U6		IC, Precision Adjustable Shunt Regulator, 1%	SOT23-5	TLV431ACDBVR	TI
1	U4		IC, High Power/Efficiency PoE PD and DC/DC Controller	HTSSOP-24	TPS23785BPWP	TI

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com