



## **Demo Note for the A8582 Evaluation Board**

**4.7V<sub>IN</sub> – 40V<sub>IN</sub>, 3.3V<sub>OUT</sub>, 2.0A, 2MHz  
Asynchronous Buck Regulator**

## GENERAL SPECIFICATIONS

| Specification                                                  | Min  | Nom  | Max  | Units |
|----------------------------------------------------------------|------|------|------|-------|
| Absolute Maximum Input Voltage                                 | -0.3 | —    | 40   | Volts |
| Operating Input Voltage Range                                  | 4.7  | 12   | 36   | Volts |
| V <sub>IN</sub> <b>START</b> Threshold, V <sub>IN</sub> rising | —    | 4.2  | 4.6  | Volts |
| V <sub>IN</sub> <b>STOP</b> Threshold, V <sub>IN</sub> falling | —    | 3.8  | 4.2  | Volts |
| Output Voltage (FB: 5.23K/16.5K, ±1%)                          | 3.20 | 3.32 | 3.44 | Volts |
| Steady-State Output Current (12V <sub>IN</sub> )               | —    | 2.0  | 2.5  | A     |
| Pulse-by-pulse Current Limit @ 30%                             | 2.6  | —    | 3.4  | A     |
| Enable/Synchronization Input                                   | -0.3 | —    | 5.5  | Volts |

## OPERATING INSTRUCTIONS

### Input Power Connection:

Connect a 12V power supply from V<sub>IN</sub> to GND that is capable of at least 2A. **Once operational, V<sub>IN</sub> can fall as low as 3.8V<sub>TYP</sub> (4.2V<sub>MAX</sub>) before the A8582 is reset.**

### Enable Input Connection:


Connect an Enable signal from EN/SYNC to GND. If the EN/SYNC input voltage is higher than 1.8V the A8582 will be enabled. If the EN/SYNC input voltage is lower than 0.8V the A8582 will be disabled. Also, EN/SYNC may be used to simultaneously enable the A8582 and synchronize the PWM switching frequency by applying a square wave above 2.2MHz.

**Note: Continuously applying more than 5.5V to the EN/SYNC pin may damage the A8582.**


### Output Load Connections:

Connect a load from V<sub>OUT</sub> to GND. The steady-state load current can be as high as 2.0A. Pulse-by-pulse current limit and/or thermal shutdown will occur if the load is greater than 4.75A.

## DEMO BOARD PICTURE



## DEMO BOARD SCHEMATIC






Note: C1 is an optional, bulk, electrolytic capacitor for general supply filtering


## DEMO BOARD BILL-OF-MATERIALS

| REFERENCE DESIGNATORS                          | DESCRIPTION                                                                | FOOTPRINT               | QTY. | MANUFACTURER              | MANUFACTURER P/N                 | SOURCE                      | PURCHASE P/N                                             |
|------------------------------------------------|----------------------------------------------------------------------------|-------------------------|------|---------------------------|----------------------------------|-----------------------------|----------------------------------------------------------|
| PCB                                            | A8583 EVAL PCB for eTSSOP16, Rev 1.1                                       | N/A                     | 1    | Allegro MicroSystems      |                                  | 4pcb.com                    |                                                          |
| U1                                             | A8582, 2A Buck Regulator                                                   | eTSSOP-16               | 1    | Allegro MicroSystems      | A8582                            |                             |                                                          |
| RFB1, RS1                                      | Resistor, 16.5Kohms, 1/10W, 1%                                             | 0603                    | 2    |                           |                                  |                             |                                                          |
| RFB2, RS2                                      | Resistor, 5.23Kohms, 1/10W, 1%                                             | 0603                    | 2    |                           |                                  |                             |                                                          |
| RFSET                                          | Resistor, 11.5Kohms, 1/10W, 1%                                             | 0603                    | 1    |                           |                                  |                             |                                                          |
| RZ                                             | Resistor, 15.4Kohms, 1/10W, 1%                                             | 0603                    | 1    |                           |                                  |                             |                                                          |
| RPU                                            | Resistor, 100Kohms, 1/10W, 1%                                              | 0603                    | 1    |                           |                                  |                             |                                                          |
| RSNUB                                          | Resistor, 4.7ohms, 1/4W, 1% or 5%                                          | 1206                    | 1    |                           |                                  |                             |                                                          |
| C1                                             | Capacitor, Electrolytic, 33uF or 47uF, 50V, <0.5ohms, -40degC to 125degC   | Thru Hole 8mm x 11.5mm  | 1    | Nichicon                  | UBW1H330MPD                      | DigiKey                     | UBW1H330MPD-ND                                           |
| CIN1                                           | Capacitor, Ceramic, 3.3uF, 50V, 10% or 20%, X5R or X7R, -55degC to 125degC | 1210 part, 1210 pads    | 1    | TDK                       | C3225X7R1H335M or C3225X7R1H335K | Digikey                     | 445-1432-1-ND                                            |
| CO1                                            | Capacitor, Ceramic, 10uF, 16V, 10%, X7R, -55degC to 125degC                | 1206 part, 1210 pads    | 1    | TDK                       | C3216X7R1C106K                   | Digikey                     | 445-3936-1-ND                                            |
| CBOOT                                          | Capacitor, Ceramic, 0.1uF, 50V, 10%, X7R                                   | 0603                    | 1    |                           |                                  |                             |                                                          |
| CSS                                            | Capacitor, Ceramic, 22nF, 25V, 10%, X7R                                    | 0603                    | 1    |                           |                                  |                             |                                                          |
| CZ                                             | Capacitor, Ceramic, 820pF, 50V, 10%, X7R                                   | 0603                    | 1    |                           |                                  |                             |                                                          |
| CP                                             | Capacitor, Ceramic, 10pF, 50V, 10%, X7R                                    | 0603                    | 1    |                           |                                  |                             |                                                          |
| CFBX                                           | Capacitor, Ceramic, 120pF, 50V, 10%, X7R                                   | 0603                    | 1    |                           |                                  |                             |                                                          |
| CSNUB                                          | Capacitor, Ceramic, 470pF, 50V, 10%, X7R                                   | 0603                    | 1    |                           |                                  |                             |                                                          |
| CO2, CO3, CO4, CO5, CIN3, CIN4, RPD, LX, RBOOT | Empty                                                                      | Various                 | 0    |                           |                                  |                             |                                                          |
| D1                                             | Schottky diode, 40V, 3A, 0.7V <sub>r</sub> @ 10A                           | SMA                     | 1    | Diodes, Inc. Central Semi | B340A-13-F B340A-13-F CSMH3-40MA | Digikey Mouser Central Semi | B340A-FDICT-ND 621-B340A-F Request samples 541-1088-1-ND |
| LO                                             | Inductor, SMT, 2.2uH, 50mohms max, 12.5Asat                                | 5.2mm x 5.5mm 2mm thick | 1    | Vishay                    | IHL2020BZER2R2M01                | Digikey Mouser              | 70-IHL2020BZER2R2M0                                      |
| VIN, EN/SYNC, SW, POK, VOUT                    | Test Points, Red, 0.063" diameter                                          | 0.063"                  | 5    | Keystone                  | 5010                             | Digikey                     | 5010K-ND                                                 |
| GND (Vout, VIN, EN/SYNC, SW)                   | Test Points, Black, 0.063" diameter                                        | 0.063"                  | 4    | Keystone                  | 5011                             | Digikey                     | 5011K-ND                                                 |
| Rubber Feet                                    | Self stick rubber feet                                                     | Clear                   | 4    | 3M                        | SJ-5303 (CLEAR)                  | Digikey                     | SJ5303-7-ND                                              |

## DEMO BOARD PERFORMANCE









| Iout<br>(A)  | A8582<br>(deg C) | D1<br>(deg C) | Lo<br>(deg C) |
|--------------|------------------|---------------|---------------|
| 0.25         | 31.3             | 31.0          | 29.5          |
| 0.5          | 34.8             | 35.4          | 32.5          |
| 1.0          | 39.9             | 42.9          | 37.2          |
| 1.5          | 44.9             | 50.6          | 42.8          |
| 2.0          | 50.9             | 58.6          | 49.3          |
| 2.5          | 57.7             | 67.8          | 57.3          |
| Shorted Vout | 30.0             | 34.9          | 29.0          |

**Component Temperatures vs Load Current**  
12Vin, 3.3Vout, 2MHz, T<sub>AMB</sub>=25deg C  
No Airflow (still air)







**SWN Voltage at 12Vin, 150mA load**  
CH1=SWN (5V/DIV), 200ns/DIV



**SWN Voltage at 12Vin, 2.2A load**  
CH1=SWN (5V/DIV), 200ns/DIV




**Input Voltage Ripple at 12Vin, 2.2A load**  
CH1=Vin across CIN1 (50mV/DIV)




**Output Shorted, Hiccup Mode Operation**  
CH1=Vout, CH2=COMP, CH3=SS, CH4=IL




## DEMO PCB LAYOUT:




Top Layer and Top Silk



Layer 2 and Top Silk



Layer 3 and Top Silk



Bottom Layer and Top Silk