

Bill of Materials

TI DESIGNS
TIDA-00315

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
1	1	!PCB1	Printed Circuit Board	Any	TIDA-00315	Fitted
2	1	C1	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Cap, 7x12x9 mm	MuRata	DE1E3KX222MA4BL01	Fitted
3	1	C2	CAP, CERM, 4700 pF, 250 V, +/- 10%, X7R, 0805	MuRata	GRM21AR72E472KW01D	Fitted
4	2	C3, C4	CAP ALUM 330UF 35V 20% RADIAL	Panasonic Electronic Components	EEU-EB1V331	Fitted
5	1	C5	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0805	Kemet	C0805C104K5RACTU	Fitted
6	1	C6	CAP, CERM, 0.1 µF, 250 V, +/- 10%, X7R, 1206	TDK	C3216X7R2E104K	Fitted
7	1	C7	CAP, ALUM, 22UF, 500V, 20%, RADIAL	NICHICON	UCY2H220MHD	Fitted
8	3	C8, C13, C14	CAP ALUM 100UF 35V 20% RADIAL	Nichicon	UPV1V101MGD1TD	Fitted
9	1	C9	CAP, Film, 0.1 µF, 305 V, +/- 20%, TH	EPCOS Inc	B32921C3104M	Fitted
10	3	C10, C11, C12	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Radial D8x5mm	MuRata	DE2E3KY222MA2BM01	Fitted
11	1	C15	CAP, AL, 220 µF, 35 V, +/- 20%, 0.09 ohm, TH	Panasonic	EEU-FC1V221	Fitted
12	1	C16	CAP, CERM, 10 µF, 25 V, +/- 10%, X5R, 0805	TDK	C2012X5R1E106K125AB	Fitted
13	1	C18	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NPO, 0805	AVX	08055A101JAT2A	Fitted
14	1	C20	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0805	Kemet	C0805C104K4RACTU	Fitted
15	2	C21, C26	CAP, CERM, 4.7 µF, 50 V, +/- 10%, X7R, 1206	MuRata	GRM31CR71H475KA12L	Fitted
16	2	C22, C27	CAP, CERM, 10 µF, 25 V, +/- 10%, X5R, 1206	Taiyo Yuden	TMK316BJ106KL-T	Fitted
17	1	C23	CAP, CERM, 8200 pF, 25 V, +/- 5%, COG/NPO, 0805	TDK	C2012COG1E822J	Fitted
18	1	C24	CAP, CERM, 47 pF, 50 V, +/- 5%, COG/NPO, 0805	AVX	08055A470JAT2A	Fitted
19	1	C25	CAP, CERM, 1500 pF, 50 V, +/- 10%, X7R, 0805	Yageo America	CC0805KRX7R9BB152	Fitted
20	7	D1, D4, D5, D6, D14, D15, D16	Diode, P-N, 1000V, 1A, TH	Fairchild Semiconductor	1N4007	Fitted
21	1	D2	DIODE, Transient Voltage Suppressor, xV, yA, 600W	ST	P6KExxx	Fitted
22	1	D3	Diode, Zener, 27 V, 500 mW, SOD-123	Diodes Inc.	MMSZ5254B-7-F	Fitted
23	1	D7	DIODE, GEN PURP, 400V, 4A, DO201AD, TH	ON SEMICONDUCTOR	MUR440	Fitted
24	2	D8, D9	Diode, Switching, 600V, 1A, TH	Vishay-Semiconductor	1N4937-E3	Fitted
25	4	D10, D17, D20, D26	Diode, Zener, 18 V, 500 mW, SOD-123	Diodes Inc.	MMSZ5248B-7-F	Fitted
26	5	D11, D13, D19, D25, D27	LED, Green, TH	Everlight	HLMP1523	Fitted

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
27	4	D12, D18, D21, D22	DIODE SUPERFAST 200V 3A SMC	Diodes Incorporated	MURS320-13-F	Fitted
28	1	D23	DIODE SMALL SIGNAL 80V 0.1A 2UMD	Rohm	1SS355TE-17	Fitted
29	1	D28	Diode, Zener, 7.5 V, 500 mW, SOD-123	Vishay-Semiconductor	MMSZ4693-V	Fitted
30	1	D29	Diode, Schottky, 40 V, 3 A, SMA	Diodes Inc.	B340A-13-F	Fitted
31	6	FID1, FID2, FID3, FID4, FID5, FID6	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	Fitted
32	4	H1, H2, H3, H4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	B&F Fastener Supply	NY PMS 440 0025 PH	Fitted
33	1	HS1	HEATSINK TO-218/TO-247 W/PINS 2"	Aavid	513201B02500G	Fitted
34	1	J1	Terminal Block, 3x1, 6.35 mm, TH	Phoenix Contact	1714968	Fitted
35	1	J2	Terminal Block, 3x1, 2.54 mm, TH	Phoenix Contact	1725669	Fitted
36	5	J3, J5, J6, J7, J8	Terminal Block, 100mil, 2x1, 6A, 63V, TH	Phoenix Contact	1725656	Fitted
37	1	J4	Terminal Block, 3x1, 9.52MM, TH	Phoenix Contact	1714984	Fitted
38	1	L1	Inductor, Unshielded Drum Core, Ferrite, 4.7 µH, 3.7 A, 0.019 ohm, TH	Wurth Elektronik	7447462047	Fitted
39	2	L2, L3	Inductor, Shielded Drum Core, Metal Composite, 1 mH, 0.5 A, 1.7 ohm, TH	Wurth Elektronik	768772102	Fitted
40	1	L4	Inductor, Shielded Drum Core, Metal Composite, 10 µH, 4.2 A, 0.0175 ohm, TH	Wurth Elektronik	7447471100	Fitted
41	1	LBL1	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	Brady	THT-14-423-10	Fitted
42	1	Q1	MOSFET, N-CH, 650 V, 15 A, TO-220 FullPAK	Infineon Technologies	AOT7S65	Fitted
43	2	Q2, Q4	MOSFET, N-CH, 60V, 0.36A, SOT-23	NXP Semiconductor	2N7002P,215	Fitted
44	1	R1	RES, 20 k, 5%, 2 W, TH	Vishay-Bccomponents	PR02000202002JR500	Fitted
45	1	R2	RES, 28.7 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080528K7FKEA	Fitted
46	1	R3	RES, 1.78 M, 1%, 0.125 W, 0805	Vishay-Dale	CRCW08051M78FKEA	Fitted
47	3	R4, R5, R6	RES, 10.0 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080510K0FKEA	Fitted
48	2	R7, R10	RES, 2.00Meg ohm, 1%, 0.25W, 1206	Panasonic	ERJ-8ENF2004V	Fitted
49	1	R8	RES, 10 k, 5%, 0.125 W, 0805	Vishay-Dale	CRCW080510K0JNEA	Fitted
50	1	R9	RES, 205, 1%, 0.125 W, 0805	Vishay-Dale	CRCW0805205RFKEA	Fitted
51	1	R11	RES, 86.6 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080586K6FKEA	Fitted
52	1	R12	RES, 18 k, 5%, 0.125 W, 0805	Vishay-Dale	CRCW080518K0JNEA	Fitted
53	1	R13	RES, 750 k, 1%, 0.25 W, 1206	Vishay-Dale	CRCW1206750KFKEA	Fitted
54	1	R14	RES, 910 k, 0.5%, 0.1 W, 0805	Susumu Co Ltd	RR1220P-914-D	Fitted
55	1	R15	RES, 44.2 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080544K2FKEA	Fitted
56	1	R16	RES, 91, 5%, 0.125 W, 0805	Vishay-Dale	CRCW080591R0JNEA	Fitted
57	1	R17	RES, 36.5 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080536K5FKEA	Fitted
58	1	R18	RES, 28.0 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080528K0FKEA	Fitted
59	1	R19	RES, 0.3, 1%, 2 W, 2512	Stackpole Electronics Inc	CSRN2512FKR300	Fitted
60	1	R20	RES, 10.2 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080510K2FKEA	Fitted
61	1	R21	RES, 22.1 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080522K1FKEA	Fitted
62	1	R22	RES, 1.58 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW08051K58FKEA	Fitted
63	3	RF1, RF2, RF3	RES, 1.0, 5%, 1 W, TH	TT Electronics/IRC	SPP1UL1R00JLF	Fitted
64	3	RV1, RV2, RV3	Varistor 250V RMS 10MM Radial, TH	Littelfuse	V250LA10P	Fitted
65	1	T1	TRANSFORMER, EXT, THT, HORIZONTAL, TH-14P	WURTH ELEKTRONIK	EF25_CUS	Fitted
66	1	U1	IC REG CTRLR FLYBK ISO 7SOIC	Texas Instruments	UCC28711D	Fitted

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
67	1	U2	3V Under Voltage Detector, 5-pin SC-70, Pb-Free	Texas Instruments	LMS33460MG/NOPB	Fitted
68	1	U3	3.5-A, 28-V, 1-MHz, Step-Down DC-DC Converter With Eco-Mode, DDA0008H	Texas Instruments	TPS54332DDAR	Fitted
69	0	C17	CAP, CERM, 3300pF, 100V, +/-5%, X7R, 0805	AVX	08051C332JAT2A	Not Fitted
70	0	C19	CAP, CERM, 2200 pF, 100 V, +/-5%, X7R, 0805	AVX	08051C222JAT2A	Not Fitted
71	0	D24	Diode, Switching, 600V, 1A, TH	Vishay-Semiconductor	1N4937-E3	Not Fitted

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.