

**Test Data
For PMP9386
3/24/2014**



Table of Contents

1. Design Specifications	3
2. Circuit Description.....	3
3. PMP9386 Board Photos	4
4. Thermal Data.....	6
5. Efficiency	7
5.1 Efficiency Chart	7
5.2 Efficiency Data.....	7
6 Waveforms.....	8
6.1 Load Transient Response	8
6.2 Startup	9
6.3 Output Voltage Ripple and Switch Node Voltage	11
7 Loop Frequency Response	13

1. Design Specifications


Vin Minimum	14VDC
Vin Maximum	15.5VDC
Vout	24VDC
Iout	8A Max.
Approximate Switching Frequency	125KHz per Phase (250KHz Effective)

2. Circuit Description


PMP9386 is a Dual-Phase Synchronous Boost Converter which accepts an input voltage of 14Vin to 15.5Vin and provides an output of 24Vout capable of supplying a maximum of 8A of current to the load. This design was built on the PMP9309 REVC PCB (4-layered board; 2 oz. Copper on Top and Bottom layers, 1 oz. Copper on two inner layers). Design uses two LM5122 Synchronous Boost controllers and CSD18531Q5A FETs. All tests in this report were performed at the highest input current condition of 14Vin.

3. PMP9386 Board Photos

Board Dimensions: 7" x 6.5"




Board Photo (Top)



Board Photo (Bottom)


4. Thermal Data



IR thermal image taken at steady state with 14Vin and 8A load (no airflow)

5. Efficiency

5.1 Efficiency Chart




5.2 Efficiency Data

Vin (V)	Iin (A)	Vout (V)	Iout (A)	Pin (W)	Pout (W)	Efficiency (%)
14.081	1.457	24.201	0.7988	20.51602	19.33176	94.2
14.056	2.86	24.195	1.5983	40.20016	38.67087	96.2
14.031	4.265	24.193	2.3976	59.84222	58.00514	96.9
14.005	5.672	24.193	3.1968	79.43636	77.34018	97.4
13.98	7.089	24.192	3.9963	99.10422	96.67849	97.6
13.955	8.516	24.192	4.7958	118.8408	116.02	97.6
13.929	9.953	24.192	5.5951	138.6353	135.3567	97.6
13.903	11.401	24.192	6.3948	158.5081	154.703	97.6
13.877	12.86	24.191	7.1942	178.4582	174.0349	97.5
13.861	14.32	24.191	7.9935	198.4895	193.3708	97.4


6 Waveforms

6.1 Load Transient Response




Load Transient Response at 14Vin and 50%-to-100% (4A-to-8A) Load Step

6.2 Startup




Startup into No Load at 14Vin




Startup into Full (8A) Load at 14Vin

6.3 Output Voltage Ripple and Switch Node Voltage




Switch Node Voltage and Output Voltage Ripple at 14Vin and No Load ($V_{ripple} \approx 130\text{mVp-p}$)



Switch Node Voltage and Output Voltage Ripple at 14Vin and Full (8A) Load ($V_{\text{ripple}} \approx 700\text{mV}_{\text{p-p}}$)

7 Loop Frequency Response



Loop Frequency Response at 14Vin and Full (8A) Load

(Phase Margin $\approx$ 65 degrees; Gain Margin $\approx$ -8 dB; Cutoff Frequency $\approx$ 8KHz)

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.