


| TABLE OF CONTENTS | |
|-------------------|---------------------------|
| 2 | Notes & Block Diagram |
| 3 | PK22FN512VMC12 (121 MBGA) |
| 4 | Power Section |
| 5 | Peripherals |
| 6 | TWRPI Modules |
| 7 | SWD K20 |
| 8 | Elevator Connector |

| Revisions | | | |
|-----------|------------------------------|------------|----------|
| Rev | Description | Date | Approved |
| X1 | Initial Release | 06/10/13 | Ron Kim |
| X2 | Release for schematic review | 06/26/2013 | Ron Kim |
| A | Release to production | 07/01/2013 | Ron Kim |
| AX1 | Respin release to CAD | 10/07/2013 | Ron Kim |
| B | Respin release to production | 10/14/2013 | Ron Kim |
| BX1 | Removing socket | 11/12/2013 | Ron Kim |
| C | Socketless version | 12/17/2013 | Ron Kim |
| C1 | Updating LPUART0 Symbol ref. | 04/04/14 | Ron Kim |

TWR-K22F120M



Microcontroller Solutions Group
6501 William Cannon Drive West
Austin, TX 78735-8099

This document contains information proprietary to Freescale Semiconductor and shall not be used for engineering design, procurement or manufacture in whole or in part without the express written permission of Freescale Semiconductor.

Designer:
Rafael del Rey

Drawing Title:
TWR-K22F120M

Drawn by:
Rafael del Rey

Page Title:
TABLE OF CONTENTS

Approved:
Ron Kim

Size
C


Document Number
SCH-27957 PDF: SPF-27957

Rev
C1

Date: Monday, April 07, 2014Sheet 1 of 8

1. Unless Otherwise Specified:
All resistors are in ohms
All capacitors are in uF
All voltages are DC
2. Interrupted lines coded with the same letter or letter combinations are electrically connected.
3. Device type number is for reference only. The number varies with the manufacturer.
4. Special signal usage:
_B Denotes - Active-Low Signal
<> or [] Denotes - Vectored Signals
5. Interpret diagram in accordance with American National Standards Institute specifications, current revision, with the exception of logic block symbology.

Block Diagram




Power & Ground Nets

| NET | VOLTAGE | DESCRIPTION |
|-----------------|----------|---|
| P5V_TRG_SDA | 5V | Output of USB power switch controlled by the VTRG_EN signal from the OpenSDA and the ELE_PS_SENSE signal from the TWR elevator connectors. Goes to regulator input select header. |
| USB0_VBUS | 5V | USB power from primary elevator Pin A57. |
| P3V3_VOUT | 3.3V | VDD power from the regulator internal to the MCU. |
| VOUT33_K20 | 3.3V | Output of OpenSDA's K20 internal regulator to power OpenSDA's circuitry |
| P5V_ELEV | 5V | Power to the elevator boards. |
| P3V3_REG | 3.3V | Output of 3.3V regulator or from the Elevator connectors. May also be supplied externally by connecting to the board voltage select header at pins 1 and 4. |
| P1V8 | 1.8V | Output of the 1.8V regulator. |
| V_BRD | 1.8-3.3V | Output of 1.8V or 3.3V regulators as selected by the board voltage select header. May also be supplied externally by connecting to the board voltage select header at pins 3 and 4. |
| VREG_IN | 5V | Power into the on board voltage regulators. |
| P5V0_VREGIN_K22 | 5V | Power into the K21 MCU voltage regulator. It is typically derived from the K21 USB connector or the elevator USB0_VBUS pin. |
| VBAT | 1.8-3.3V | Voltage to the battery input of the MCU. The value depends on whether the board is powered and at what value and the setting of the shunt that selects the source of the battery voltage. |
| MCU_PWR | 1.8-3.3V | MCU digital power. Filtered from V_BRD |
| MCU_VDD | 1.8-3.3V | MCU digital power input after current measurement jumper |
| VDDA | 1.8-3.3V | VDDA power for MCU and analog circuits. Filtered from MCU_PWR. |
| P3V3_REG | 3.3V | Output of regulator U503 or from the Elevator connector |
| VREFH | 3.3V | Upper reference voltage for ADC on the MCU. Filtered from VDDA. |
| VREFL | 0V | Lower reference voltage for ADC on the MCU. Filtered from VSSA. |
| VSSA | 0V | VSSA power for MCU and analog circuits. Filtered from GND. |
| GND | 0V | Digital and Analog Ground. |




| | | | |
|---------------------------------------|--|--------|--|
| ICAP Classification: FCP: FUC: X PUB: | | | |
| Drawing Title: TWR-K22F120M | | | |
| Page Title: NOTES & BLOCK DIAGRAM | | | |
| Size C | Document Number SCH-27957 PDF: SPF-27957 | Rev C1 | |
| Date: Monday, April 07, 2014 | Sheet 2 | of 8 | |


K22F - 121MBGA



Cortex Debug+ETM Connector




K21 USB Interface (Host, Device, OTG)




BOARD POWER SELECTOR:

1-2: VOUT_3V3 (from MCU)
3-5: 3.3 V from regulator (default)
5-7: 1.8 V from regulator


System Power




PWR_MCU



GND LOOP TEST PADS




GND LOOP TEST LOOPS




CAD NOTE:
Place ground test loops in the four corners away from sensitive signals that might short with scope probe alligator clips




LEDS



GPIO Header




PUSH BUTTONS



| | | | |
|--|--|--------|--|
| ICAP Classification: FCP: FIUC: X PUB: | | | |
| Drawing Title: TWR-K22F120M | | | |
| Page Title: PERIPHERALS | | | |
| Size C | Document Number SCH-27957 PDF: SPF-27957 | Rev C1 | |
| Date: Monday, April 07, 2014 | Sheet 5 | of 8 | |

OpenSDA Interface



**You can rename
signal names in
blue/orange
boxes below
according to
your system**

Isolation Resistors

**OPEN SDA
INPUT POWER**

P3V3_SDA $\leftarrow i$ path

3.3VDC, 10mA should be provided to this rail (P3V3_SDA) in order to power openSDA module

OPEN SDA
POWER OUTPUTS

SDA_VOUT33 *i path*

Note: You can power openSDA with your own power supplies by replacing this rail (SDA_VOUT33) with your 3.3V power supply rail

P5V_TRG_SDA 

SDA_VOUT33 can provide up to 120mA of power at 3.3VDC to your system

P5V_TRG_SDA can provide up to 450mA (per USB spec) of power at 5VDC


I/O POWER INPUT

V_BRD


V_BRD is supported from 1.8V to 5V

Source should be specified

OpenSDA INTERFACE JTAG CONNECTOR




PWR SWITCH
(To enable 5v from USB connector)



OPTIONAL TOWER SPECIFIC INTERFACING CIRCUITRY

You can entirely remove the contents in this box when interfacing openSDA in a non-Tower system.


If that is the case, please populate all isolation resistors



To implement OpenSDA interface in your system:

**Copy this whole page to your schematic.
Update netnames in designed boxes
according to your system net naming.**

ELEVATOR CONNECTOR



Note that signals coming from the elevator are usually 3.3V. They should not be used when the board is configured for 1.8V operation.



| | | | | |
|----------------------|---|------|---------|-----------|
| ICAP Classification: | | FCP: | FIUO: X | PUBI: |
| Drawing Title: | | | | |
| TWR-K22F120M | | | | |
| Page Title: | | | | |
| ELEVATORS | | | | |
| Size C | Document Number SCH-27957 PDF: SPF-27957 | | | Rev C1 |
| Date: | Monday, April 07, 2014 | | Sheet | 6 of 6 |