

SIZE	QTY	SYM	PLATED	TOL
0.006	2	$\text{+}^{\text{A}}$	YES	$\pm 0.003$
0.01	162	$\text{+}^{\text{B}}$	YES	$\pm 0.003$
0.035	19	$\text{+}^{\text{C}}$	YES	$\pm 0.003$
0.095	6	$\times$	YES	$\pm 0.003$
0.07	2	$\diamond$	NO	$\pm 0.003$


#### ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

#### ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:


1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
2. SOLDERABILITY BOARD WITH TEST RESULTS.
3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
4. VACUUM PACKED WITH DESICCANT.
5. FULL PANEL WITH NO REJECT

## LAYER STRUCTURE



## NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4  
-FINISHED THICKNESS TO BE 0.062"  $\pm 0.005$ "  
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.  
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.  
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
-HOLE LOCATION TOLERANCES ARE  $\pm 0.003$ " IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.  
-GOLD IMMERSION BOTH SIDES.  
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)  
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



UNLESS OTHERWISE SPECIFIED				1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL - FOR CUSTOMER USE ONLY
DIMENSIONS ARE IN INCHES		TITLE: FABRICATION DRAWING		
TOLERANCES:		45V VIN, 500ma LOW NOISE LINEAR REGULATOR WITH		
0.XX" = $\pm 0.01$ "		PROGRAMMABLE CURRENT LIMIT AND OUTPUT DISCHARGE		
0.XXX" = $\pm 0.005$ "		SIZE IC NO. LT3066EDE		
INTERPRET DIM AND TOL		N/A DEMO CIRCUIT 2437A		
PER ASME Y14.5M-1994		REV 2		
THIRD ANGLE PROJECTION		FILENAME: DC2437A-2.PCB		
		SHT 1 OF 1		