


**200 Krad(Si) Low Dropout
Linear Regulator
Hermetic Package**

**OMR9800SC
OMR9800SF
+ 3.3V_{in} to +1.8V_{out} at 3.0A**

Product Summary

Part Number	I _o	V _{in}	V _{out}	Package
OMR9800SC	3.0A	3.3V	1.8V	MO-078AA
OMR9800SF	3.0A	3.3V	1.8V	8-pin Flatpack



The OMR9800 is a radiation hardened, low dropout linear regulator designed specifically for space applications. This product has been characterized to a total ionizing dose of 200 Krad (Si) per MIL-STD-883, Method 1019, Condition A at both high and low dose rates under biased and unbiased conditions to account for ELDRS effects in bipolar devices. The ultra low dropout voltage of 1.1V @ 3A makes the part particularly useful for applications requiring low noise and higher efficiency.

Features:

- Total dose and low dose capability to 200 Krad(Si) allows use in space applications
- Low dropout of 1.1 volts significantly reduces power consumption
- Low noise, higher efficiency
- Remote shutdown permits power sequencing to be easily implemented
- Hermetic MO-078AA (TO-258AA) and 8-lead flat pack ensure higher reliability
- K-level screened

Absolute Maximum Ratings


Symbol	Parameter	Value	Units
I _o	Output Current	3.5	A
V _{in}	Input Voltage	+7.0	V
P _{TOT}	Power Dissipation TC=25 °C	19	W
R _{THJC}	Thermal Resistance, Junction to Case (MO-078AA)	6.5	°C/W
R _{THJC}	Thermal Resistance, Junction to Case (8 lead flatpack)	6.5	°C/W
T _J	Operating Junction	-55 to +125	°C
T _{STG}	Storage Temperature Range	-65 to +150	°C
T _L	Lead Temperature	300	°C



Electrical Characteristics @ TA= 25°C (Unless Otherwise Specified)

Parameter	Conditions	Symbol	Min.	Typ.	Max	Unit
Output Voltage	Vin= 3.3V, Io= 3.0A	Vout	1.782	1.8	1.818	V
Input Voltage Range- Operating	Io= 3.0A		2.9		6.5	V
Line Regulation	3.13 ≤ Vin ≤ 3.46, Io= 3.0A	Vline	-100		+100	mV
	2.9 ≤ Vin ≤ 3.8, Io= 50mA		-5		+5	mV
Load Regulation	Vin= 3.3V 10ma ≤ Iout ≤ 3.0A	Vload	-20		+20	mV
Dropout Voltage	Io= 3.0A, Vout= 1.8V	Vdrop			1.1	V
Current Limit	Vin= 3.3V, Overcurrent Latchup	I latch	3			A
Ripple Rejection	F= 120 Hz., Vout= Vref		65			dB
Shutdown Source Current	Vshdn= 5V	Ishdn		200		uA
Shutdown Pin Threshold	Isource= 200uA	Vshdn	1		1.6	V
Output Voltage at Shutdown	Vin= 3.3V, Io= 50mA, Shdn= +5.0V	Vout (shdn)	-0.1		+0.1	V

Electrical Characteristics TA= -55 to +125°C

Parameter	Conditions	Symbol	Min.	Typ.	Max	Unit
Output Voltage	Vin= 3.3V, Io= 3.0A	Vout	1.71	1.8	1.89	V
Input Voltage Range- Operating	Io= 3.0A		2.9		6.5	V
Line Regulation	3.13 ≤ Vin ≤ 3.46, Io= 3.0A	Vline	-150		+150	mV
	2.9 ≤ Vin ≤ 3.8, Io= 50mA		-150		+150	mV
Load Regulation	Vin= 3.3V 10ma ≤ Iout ≤ 3.0A	Vload	-150		+150	mV
Dropout Voltage	Io= 3.0A, Vout= 1.8V	Vdrop			1.1	V
Current Limit	Vin= 3.3V, Overcurrent Latchup	I latch	3			A
Ripple Rejection	F= 120 Hz., Vout= Vref		65			dB
Shutdown Source Current	Vshdn= 5V	Ishdn		200		uA
Shutdown Pin Threshold	Isource= 200uA	Vshdn	1		1.6	V
Output Voltage at Shutdown	Vin= 3.3V, Io= 50mA, Shdn= +5.0V	Vout (shdn)	-0.1		+0.1	V

Simplified Schematic




In order to maintain regulation and stability specified additional input and output bulk capacitors are recommended. Capacitors recommended above should be low ESR tantalums with tolerances of +/- 20% max. Internal to the product are a 4.7uF input capacitor and a 4.7uF output capacitor in parallel with a 0.33uF ceramic capacitor.

Shutdown: The regulator can be shutdown by applying a voltage >1.6V to pin 4. The regulator will restart when the SHDN pin is pulled below the shutdown threshold of 1.0V. If remote shutdown is not required, pin 4 should be connected to GND to insure a safe "off" state

Mechanical Outline MO-078AA

Base: GLIDCOP
Pins: Copper core, Alloy 52
Seals: Glass


Pin Connections	
Terminal	Description
1	Vin
2	GND
3	Vout
4	Shutdown
5	No Connection



Mechanical Outline 8-Lead Flat Pack

Base: 1010-1018 C.R.S.
Pins: #52 Alloy, Copper Cored
Seals: Glass – 9013 or Equiv.
Finish: 100-250 Microinches Electroless Nickel Over 50-250 Microinches Electrolytic Nickel.

Pin Connections	
Terminal	Description
1,2	GND
3	Shutdown
4	No Connection
5,6	Vout
7,8	Vin



Part Number Nomenclature

<u>OM</u>	<u>R</u>	<u>9800</u>	<u>X</u>	<u>X</u>	<u>X</u>
Omnirel	Radiation Hardened/Tolerant	Device	S=Isolated N=Non-Isolated	Package	Screening

Part Number	Package Description	Screening
OMR9800SCP	MO-078AA 5 - Lead	100% Final Electrical
OMR9800SCH	MO-078AA 5 - Lead	Class H per MIL-PRF-38534
OMR9800SCK	MO-078AA 5 - Lead	Class K per MIL-PRF-38534
OMR9800SFP	8 -Lead Flat Pack	100% Final Electrical
OMR9800SFH	8 -Lead Flat Pack	Class H per MIL-PRF-38534
OMR9800SFK	8 -Lead Flat Pack	Class K per MIL-PRF-38534

MIL-PRF-38534 Screening Requirements

TEST/INSPECTION	SCREENING LEVEL		MIL-STD-883
	Class H	Class K (Space Level)	Method
Pre Seal Burn-In	Optional	Optional	1030
Nondestructive Bond Pull	N/A	100%	2023
Internal Visual	100%	100%	2017
Temperature Cycle	100%	100%	1010
Constant Acceleration	100%	100%	2001
Mechanical Shock	100%	100%	2002
PIND	N/A	100%	2020
Pre Burn-In Electrical	Optional	100%	
Burn-In	100%	100%	1015
Final Electrical	100%	100%	
Seal	100%	100%	1014
Radiographic	N/A	100%	2012
External Visual	100%	100%	2009