2017-10-30 Rev.1.0

TOSHIBA

RD Number: RD054

RD Title: TB67H420FTG Evaluation circuit

Item No.	Designator	Quantity	Value	Part Number	Manufacturer	Description	Package	Not Mount
NO.	CVM1	Quantity	1 100µF	UHE1H101MPD	Manufacturei	Electrolytic capacitor	Раскауе	Not Mount
1		-	<u> </u>	C3216+TH0.9-P6.8		· ·	3.2mmX1.6mm	
2	CVM2	:	1 0.1μF			Chip capacitor		
	CVCC		1 0.1μF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	
-	CVFA	-	1 0.1μF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	
	CVFB	+	1 0.1μF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	
6	C13	(1000pF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	✓
7	C17	(1000pF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	✓
8	C19	(1000pF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	✓
9	C23	(1000pF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	✓
10	COSCM		1 270pF	C3216+TH0.9-P6.8		Chip capacitor	3.2mmX1.6mm	
11	ROSCM		₁ 5.1kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	
12	RMO	(10kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	✓
13	RLO1		1 10kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	
14	RLO2		1 10kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	
15	RVF1		₁ 20kΩ,1/8W	Leaded resistor		Leaded resistor		
16	RVF2		₁ 10kΩ,1/8W	Leaded resistor		Leaded resistor		
17	RVF3		₁ 10kΩ,1/8W	Leaded resistor		Leaded resistor		
18	RVF1		2 -	PD-10		Socket pin		
19	RVF2	:	2 -	PD-10		Socket pin		
20	RVF3		2 -	PD-10		Socket pin		
	RLTH		100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√
22	RCLIM11		100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√
23	RCLIM12		100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√
24	RFLIM1	(100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√
	RFLIM2		100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√
	RBOOST1	(100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	√

27 RBOOST2	0 100kΩ	C3216+TH0.9-P6.8		Chip resistor	3.2mmX1.6mm	✓
28 CNSRI	0 -	DF1BZ-3P-2.5DSA	Hirose Electric	Connector		✓
29 CNSRO	0 -	DF1BZ-3P-2.5DSA	Hirose Electric	Connector		✓
30 CNMT	1 -	DF1BZ-4P-2.5DSA	Hirose Electric	Connector		
31 SW_39	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
32 SW_40	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
33 SW_41	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
34 SW_42	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
35 SW_43	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
36 SW_44	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
37 SW_45	0 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		✓
38 SW_AGC0	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
39 SW_AGC1	1 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		
40 SW_CLIM0	0 -	ATE1E-2M3-10-Z	Copal Electronics	Toggle Switches		✓
41 SW_CLIM1	0	S-2150	Copal Electronics	Rotary Switch		✓
42 SW_FLIM	0	S-2150	Copal Electronics	Rotary Switch		✓
43 SW_BOOST	0	S-2150	Copal Electronics	Rotary Switch		✓
44 DO	0 -	ST-1-3	Mac8	Check pin		✓
45 CO	0 -	ST-1-3	Mac8	Check pin		✓
46 LO	0 -	ST-1-3	Mac8	Check pin		✓
47 VREFA	1 -	ST-1-3	Mac8	Check pin		
48 VREFB	1 -	ST-1-3	Mac8	Check pin		
49 SVF	1 -	ST-1-3	Mac8	Check pin		
50 39	1 -	ST-1-3	Mac8	Check pin		
51 40	1 -	ST-1-3	Mac8	Check pin		
52 41	1 -	ST-1-3	Mac8	Check pin		
53 42	1 -	ST-1-3	Mac8	Check pin		
54 43	1 -	ST-1-3	Mac8	Check pin		
55 44	1 -	ST-1-3	Mac8	Check pin		
₅₆ 45	0 -	ST-1-3	Mac8	Check pin		√
57 46	0 -	ST-1-3	Mac8	Check pin		✓
58 47	1 -	ST-1-3	Mac8	Check pin		
59 48	1 -	ST-1-3	Mac8	Check pin		
60 LI	0 -	ST-1-3	Mac8	Check pin		√

61 C C C C C C C C C C C C C				1	į.	l	1	
6-3 ACCO 1 1 ST-1-3 Med8 Check pin			0 -	ST-1-3	Mac8	Check pin		✓
64 ACC1 1 1 ST-1-3 Mac8 Check pin			0 -			Check pin		✓
65 CLIMO 0 - ST-1-3 Mac8 Check pin		•	1 -	ST-1-3	Mac8	Check pin		
66 CLIM1	64	AGC1	1 -	ST-1-3	Mac8	Check pin		
ST-1-3 Mac8 Check pin			0 -	ST-1-3	Mac8	Check pin		✓
68 800ST 0 ST-1-3 Mac8 Check pin J	66	CLIM1	0 -	ST-1-3	Mac8	Check pin		✓
ST-1-3 Mac8 Check pin	67	FLIM	0 -	ST-1-3	Mac8	Check pin		√
To VM	68	BOOST	0 -	ST-1-3	Mac8	Check pin		√
T1 GND1	69	VDD	1 -	ST-1-3	Mac8	Check pin		
72 GND2 1 - ST-1-3 Mac8 Check pin 73 GND3 1 - ST-1-3 Mac8 Check pin 74 GND4 1 - ST-1-3 Mac8 Check pin 75 GND5 1 - ST-1-3 Mac8 Check pin 76 GND6 1 - ST-1-3 Mac8 Check pin 77 GND7 1 - ST-1-3 Mac8 Check pin 78 GND8 1 - ST-1-3 Mac8 Check pin 79 GND9 1 - ST-1-3 Mac8 Check pin 80 GND10 1 - ST-1-3 Mac8 Check pin 81 GND11 1 - ST-1-3 Mac8 Check pin 82 TVF 1 - RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 - - Jumper - 84 (JP1) 1 - Jumper - 86 (JP2)	70	VM	1 -	ST-1-3	Mac8	Check pin		
73 GND3 1 - ST-1-3 Mac8 Check pin 74 GND4 1 - ST-1-3 Mac8 Check pin 75 GND5 1 - ST-1-3 Mac8 Check pin 76 GND6 1 - ST-1-3 Mac8 Check pin 77 GND7 1 - ST-1-3 Mac8 Check pin 78 GND8 1 - ST-1-3 Mac8 Check pin 79 GND9 1 - ST-1-3 Mac8 Check pin 80 GND10 1 - ST-1-3 Mac8 Check pin 81 GND11 1 - ST-1-3 Mac8 Check pin 82 TVF 1 - RN1401 TOSHBA Bias Resistor Built-in Transistor 83 JP1 1 - Jumper Jumper 84 (JP1) 1 - Jumper 86 (JP2) 1 - Jumper 86 (JP2) 1 - Jumper	71	GND1	1 -	ST-1-3	Mac8	Check pin		
73 GND3 1 - ST-1-3 Mac8 Check pin 74 GND4 1 - ST-1-3 Mac8 Check pin 75 GND5 1 - ST-1-3 Mac8 Check pin 76 GND6 1 - ST-1-3 Mac8 Check pin 77 GND7 1 - ST-1-3 Mac8 Check pin 78 GND8 1 - ST-1-3 Mac8 Check pin 79 GND9 1 - ST-1-3 Mac8 Check pin 80 GND10 1 - ST-1-3 Mac8 Check pin 81 GND11 1 - ST-1-3 Mac8 Check pin 82 TVF 1 - RN1401 TOSHBA Bias Resistor Built-in Transistor 83 JP1 1 - Jumper Jumper 84 (JP1) 1 - Jumper 86 (JP2) 1 - Jumper 86 (JP2) 1 - Jumper			1 -	ST-1-3	Mac8	Check pin		
ST-1-3 Mac8 Check pin ST-1-3 ST-1-3 ST-1-3 ST-1-3 Mac8 Check pin ST-1-3 ST-1-3	73	GND3	1 -	ST-1-3	Mac8	Check pin		
76 GND6 1 - ST-1-3 Mac8 Check pin 77 GND7 1 - ST-1-3 Mac8 Check pin 78 GND8 1 - ST-1-3 Mac8 Check pin 80 GND9 1 - ST-1-3 Mac8 Check pin 80 GND10 1 - ST-1-3 Mac8 Check pin 81 GND11 1 - ST-1-3 Mac8 Check pin 82 TVF 1 - RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 - Jumper - 84 JP1) 1 - Jumper - 85 JP2 1 - Jumper - 86 JP2) 1 - Jumper - 87 IC1 1 TB67H420FTG TOSHIBA IC IC	74	GND4	1 -	ST-1-3	Mac8	Check pin		
77 GND7 1 ST-1-3 Mac8 Check pin 1 78 GND8 1 ST-1-3 Mac8 Check pin 1 79 GND9 1 ST-1-3 Mac8 Check pin 1 80 GND10 1 ST-1-3 Mac8 Check pin 1 81 GND11 1 ST-1-3 Mac8 Check pin 1 82 TVF 1 RN1401 TOSHIBA Bias Resistor Built-in Transistor 1 83 JP1 1 NUMPER NUMPER NUMPER NUMPER NUMPER 84 (JP1) 1 NUMPER NUMPER <t< td=""><td>75</td><td>GND5</td><td>1 -</td><td>ST-1-3</td><td>Mac8</td><td>Check pin</td><td></td><td></td></t<>	75	GND5	1 -	ST-1-3	Mac8	Check pin		
78 GND8 1 ST-1-3 Mac8 Check pin ————————————————————————————————————	76	GND6	1 -	ST-1-3	Mac8	Check pin		
79 GND9 1 - ST-1-3 Mac8 Check pin 80 GND10 1 - ST-1-3 Mac8 Check pin 81 GND11 1 - ST-1-3 Mac8 Check pin 82 TVF 1 - RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 - Jumper Jumper 84 (JP1) 1 Jumper Jumper 85 JP2 1 - Jumper Jumper 86 (JP2) 1 TB67H420FTG TOSHIBA IC 87 IC1 1 TB67H420FTG TOSHIBA IC	77	GND7	1 -	ST-1-3	Mac8	Check pin		
80 GND10 1 ST-1-3 Mac8 Check pin 81 GND11 1 ST-1-3 Mac8 Check pin 82 TVF 1 RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 Jumper 84 (JP1) 1 Jumper 85 JP2 1 Jumper 86 (JP2) 1 Jumper 87 IC1 1 TB67H420FTG TOSHIBA IC 88 IC IC IC	78	GND8	1 -	ST-1-3	Mac8	Check pin		
80 GND10 1 ST-1-3 Mac8 Check pin 81 GND11 1 ST-1-3 Mac8 Check pin 82 TVF 1 RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 Jumper 84 (JP1) 1 Jumper 85 JP2 1 Jumper 86 (JP2) 1 Jumper 87 IC1 1 TB67H420FTG TOSHIBA IC 88 IC IC IC	79	GND9	1 -	ST-1-3	Mac8	Check pin		
82 TVF 1 - RN1401 TOSHIBA Bias Resistor Built-in Transistor 83 JP1 1 - Jumper - 84 (JP1) 1 - Jumper - 85 JP2 1 - Jumper - - 86 (JP2) 1 TB67H420FTG TOSHIBA IC IC - - 88 1 TB67H420FTG TOSHIBA IC - - -	80	GND10	1 -	ST-1-3	Mac8	Check pin		
83 JP1 1 - Jumper Jumper 84 (JP1) 1 Jumper Jumper 85 JP2 1 - Jumper Jumper 86 (JP2) 1 TB67H420FTG TOSHIBA IC 87 IC1 1 TB67H420FTG TOSHIBA IC 88 IC IC IC	81	GND11	1 -	ST-1-3	Mac8	Check pin		
84 (JP1) 1 5 JP2 1 - Jumper Jumper 5 JP2 1 - 5 JP2 1 JP2	82	TVF	1 -	RN1401	TOSHIBA	Bias Resistor Built-in Transistor		
85 JP2 1 - Jumper Jumper 86 (JP2) 1 TB67H420FTG TOSHIBA IC 87 IC1 1 TB67H420FTG TOSHIBA IC 88 IC IC IC	83	JP1	1 -			Jumper		
86 (JP2) 1 87 IC1 1 88 ICI 1 1 ICI			1					
86 (JP2) 1 87 IC1 1 88 ICI 1 1 ICI	85	JP2	1 -			Jumper		
87 IC1 1 TB67H420FTG TOSHIBA IC 88 IC IC IC			1					
88			1	TB67H420FTG	TOSHIBA	IC		
 								
90								
91								
92								
93								
	94							

95				
96				
97				
98				
99				
100				

Terms of Use

This terms of use is made between Toshiba Electronic Devices and Storage Corporation ("We") and customers who use documents and data that are consulted to design electronics applications on which our semiconductor devices are mounted ("this Reference Design"). Customers shall comply with this terms of use. Please note that it is assumed that customers agree to any and all this terms of use if customers download this Reference Design. We may, at its sole and exclusive discretion, change, alter, modify, add, and/or remove any part of this terms of use at any time without any prior notice. We may terminate this terms of use at any time and for any reason. Upon termination of this terms of use, customers shall destroy this Reference Design. In the event of any breach thereof by customers, customers shall destroy this Reference Design, and furnish us a written confirmation to prove such destruction.

1. Restrictions on usage

- 1. This Reference Design is provided solely as reference data for designing electronics applications. Customers shall not use this Reference Design for any other purpose, including without limitation, verification of reliability.
- 2. This Reference Design is for customer's own use and not for sale, lease or other transfer.
- 3. Customers shall not use this Reference Design for evaluation in high or low temperature, high humidity, or high electromagnetic environments.
- 4. This Reference Design shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.

2. Limitations

- 1. We reserve the right to make changes to this Reference Design without notice.
- 2. This Reference Design should be treated as a reference only. We are not responsible for any incorrect or incomplete data and information.
- 3. Semiconductor devices can malfunction or fail. When designing electronics applications by referring to this Reference Design, customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of semiconductor devices could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Customers must also

- refer to and comply with the latest versions of all relevant our information, including without limitation, specifications, data sheets and application notes for semiconductor devices, as well as the precautions and conditions set forth in the "Semiconductor Reliability Handbook".
- 4. When designing electronics applications by referring to this Reference Design, customers must evaluate the whole system adequately. Customers are solely responsible for all aspects of their own product design or applications. WE ASSUME NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- 5. No responsibility is assumed by us for any infringement of patents or any other intellectual property rights of third parties that may result from the use of this Reference Design. No license to any intellectual property right is granted by this terms of use, whether express or implied, by estoppel or otherwise.
- 6. THIS REFERENCE DESIGN IS PROVIDED "AS IS". WE (a) ASSUME NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (b) DISCLAIM ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO THIS REFERENCE DESIGN, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.

3. Export Control

Customers shall not use or otherwise make available this Reference Design for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). This Reference Design may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of this Reference Design are strictly prohibited except in compliance with all applicable export laws and regulations.

4. Governing Laws

This terms of use shall be governed and construed by laws of Japan.