

RD Number: RD114

RD Title: TC78B006FNG Evaluation circuit

Item No.	Designator	Quantity	Value	Part Number	Manufacturer	Description	Package	Not Mount
1	IC1	1		TC78B006FNG	Toshiba	single phase pre-driver		
2	IC2	1		LT1121CST-5	Linear Technology	5V regulator		
3	IC3	1		TLC555QDR	Texas Instruments	OSC Timer		
4	D1	1		CUS10I40A	Toshiba			
5	D2	1		CUS10I40A	Toshiba			
6	FET1	1		TPCP8406	Toshiba			
7	FET2	1		TPCP8406	Toshiba			
8	LED1	1		SMLE12P8WT86	Rohm	LED (Green)		
9	LED2	1		SMLE13BC8TT86	Rohm	LED (Blue)		
10	CVM1	1	10uF, 50V, JB	C3216JB1H106K160AB	TDK	CAP, CER	1206 (3212)	
11	CVM2	1	0.1uF, 50V, B	GRM188B31H104KA92		CAP, CERM	1608	
12	C1	1	1uF, 50V, X5R	GRM31MB31H105KA87		CAP, CERM	3212	
13	C2	1	1uF, 50V, X5R	GRM31MB31H105KA87		CAP, CERM	3212	
14	C3	1	0.1uF, 50V, B	GRM188B31H104KA92		CAP, CERM	1608	
15	C4	1	0.01uF, 50V, B	GRM188B11H103KA01D		CAP, CERM	1608	
16	CCONT	1	0.01uF, 50V, B	GRM188B11H103KA01D		CAP, CERM	1608	
17	CVREG	1	0.1uF, 50V, B	GRM188B31H104KA92		CAP, CERM	1608	
18	CHALL	0				open		✓
19	CVSP	0				open		✓
20	COC	0				open		✓
21	RPWM	1	10k ohm, 5%, 0.1W	RK73B1JTTD103J	KOA	RES	1608	
22	RP	1	51k ohm, 5%, 0.1W	RK73B1JTTD513J	KOA	RES	1608	
23	RF/R	1	51k ohm, 5%, 0.1W	RK73B1JTTD513J	KOA	RES	1608	
24	RVSP	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
25	ROC	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
26	RHB	1	1k ohm, 5%, 0.1W	RK73B1JTTD102J	KOA	RES	1608	

27	RLED_1	1	5.1k ohm, 5%, 0.1W	RK73B1JTTD512J	KOA	RES	1608	
28	RLED_2	1	5.1k ohm, 5%, 0.1W	RK73B1JTTD512J	KOA	RES	1608	
29	R1P1	1	1k ohm, 5%, 0.1W	RK73B1JTTD102J	KOA	RES	1608	
30	R2P1	1	1k ohm, 5%, 0.1W	RK73B1JTTD102J	KOA	RES	1608	
31	R1P2	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
32	R2P2	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
33	R1N1	0				open		✓
34	R2N1	0				open		✓
35	R1N2	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
36	R2N2	1	0 ohm, 1A	RK73Z1JTTD	KOA	RES	1608	
37	RS1	1	0.1ohm, 1%,0.5W	ERJ14BSFR10U		RES	3225	
38	VR1	1	5.0K OHM	3352T-1-502LF	Bourns	POT THUMBWHEEL CERM ST		
39	VR2	1	50K OHM 0.25W	PVG3A503C01R00	Bourns	TRIMMER SMD		
40	VR3	1	50K OHM 0.25W	PVG3A503C01R00	Bourns	TRIMMER SMD		
41	VR4	1	50K OHM 0.25W	PVG3A503C01R00	Bourns	TRIMMER SMD		
42	OUT1	1		ST-1-3	MAC8	Logic pin		
43	OUT2	1		ST-1-3	MAC8	Logic pin		
44	VM	1		ST-1-3	MAC8	Logic pin		
45	GND	1		ST-1-3	MAC8	Logic pin		
46	FG RDO	1		ST-1-3	MAC8	Logic pin		
47	TSP VSP	1		ST-1-3	MAC8	Logic pin		
48	VMI	1		ST-1-3	MAC8	Logic pin		
49	VSOFT	1		ST-1-3	MAC8	Logic pin		
50	SS	1		ST-1-3	MAC8	Logic pin		
51	CT	1		ST-1-3	MAC8	Logic pin		
52	HM	1		ST-1-3	MAC8	Logic pin		
53	HP	1		ST-1-3	MAC8	Logic pin		
54	HB	1		ST-1-3	MAC8	Logic pin		
55	CN1	1		DF1BZ-2P-2.5DSA	HRS	Connector		
56	CN2	1		DF1BZ-4P-2.5DSA	HRS	Connector		
57	CN3	1		DF1BZ-2P-2.5DSA	HRS	Connector		
58	J1	1				Short		
59	J2	1		2130S1*3GSE	Linkman	Jumper		
60		1		2180BBA	Linkman	Jumper Short		

61	J3	1		2130S1*2GSE	Linkman	Jumper		
62		1		2180BBA	Linkman	Jumper Short		
63								
64								
65								
66								
67								
68								
69								
70								
71								
72								
73								
74								
75								
76								
77								
78								
79								
80								
81								
82								
83								
84								
85								
86								
87								
88								
89								
90								
91								
92								
93								
94								

95								
96								
97								
98								
99								
100								

## Terms of Use

This terms of use is made between Toshiba Electronic Devices and Storage Corporation ("We") and customers who use documents and data that are consulted to design electronics applications on which our semiconductor devices are mounted ("this Reference Design"). Customers shall comply with this terms of use. Please note that it is assumed that customers agree to any and all this terms of use if customers download this Reference Design. We may, at its sole and exclusive discretion, change, alter, modify, add, and/or remove any part of this terms of use at any time without any prior notice. We may terminate this terms of use at any time and for any reason. Upon termination of this terms of use, customers shall destroy this Reference Design. In the event of any breach thereof by customers, customers shall destroy this Reference Design, and furnish us a written confirmation to prove such destruction.

### 1. Restrictions on usage

1. This Reference Design is provided solely as reference data for designing electronics applications. Customers shall not use this Reference Design for any other purpose, including without limitation, verification of reliability.
2. This Reference Design is for customer's own use and not for sale, lease or other transfer.
3. Customers shall not use this Reference Design for evaluation in high or low temperature, high humidity, or high electromagnetic environments.
4. This Reference Design shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.

### 2. Limitations

1. We reserve the right to make changes to this Reference Design without notice.
2. This Reference Design should be treated as a reference only. We are not responsible for any incorrect or incomplete data and information.
3. Semiconductor devices can malfunction or fail. When designing electronics applications by referring to this Reference Design, customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of semiconductor devices could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Customers must also

refer to and comply with the latest versions of all relevant our information, including without limitation, specifications, data sheets and application notes for semiconductor devices, as well as the precautions and conditions set forth in the "Semiconductor Reliability Handbook".

4. When designing electronics applications by referring to this Reference Design, customers must evaluate the whole system adequately. Customers are solely responsible for all aspects of their own product design or applications. WE ASSUME NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
5. No responsibility is assumed by us for any infringement of patents or any other intellectual property rights of third parties that may result from the use of this Reference Design. No license to any intellectual property right is granted by this terms of use, whether express or implied, by estoppel or otherwise.
6. THIS REFERENCE DESIGN IS PROVIDED "AS IS". WE (a) ASSUME NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (b) DISCLAIM ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO THIS REFERENCE DESIGN, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.

### 3. Export Control

Customers shall not use or otherwise make available this Reference Design for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). This Reference Design may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of this Reference Design are strictly prohibited except in compliance with all applicable export laws and regulations.

### 4. Governing Laws

This terms of use shall be governed and construed by laws of Japan.