



Texas Instruments

PMP4344 Test Procedure

China Power Reference Design


REV A

11/07/2012

1 GENERAL

1.1 PURPOSE

To provide detailed data for evaluating and verifying the PMP4344, which uses TI new Primary Side Controller UCC28710 for USB charger with 22mmx21mmx20mm. The below photo shows this demo board.



1.2 REFERENCE DOCUMENTATION

Schematic PMP4344_SCH.PDF

Assembly PMP4344_PCB.PDF

BOM

Promotion tools

1.3 TEST EQUIPMENTS

Power-meter: YOKOGAWA WT210

Multi-meter(current): Fluke 8845A


Multi-meter(voltage): Fluke 187

AC Source: Chroma 61530

LED load: Chroma 63110A module


2 INPUT CHARACTERISTICS
Otherwise Specified, the test is under the condition With 1m USB cable

2.1 STANDBY POWER




2.2 LOAD AND INPUT VOLTAGE VS EFFICIENCY

Notes: efficiency test is based USB port




2.3 AVERAGE EFFICIENCY AT 0.25A, 0.5A, 0.75A AND 1A

Notes: efficiency test is based USB port



2.4 EFFICIENCY VS LOAD

Notes: efficiency test is based USB port




2.5 INPUT CURRENT

Vin(Vac)	Freq(Hz)	Iin(Arms)	Pass/Fail
85	60	0.138	

2.6 INPUT INRUSH CURRENT


Max inrush current: 1.17A @264Vac and 1.2A load




3 OUTPUT CHARACTERISTICS

3.1 STARTUP TIME

Input voltage	Output current	Startup time	Pass/Fail
115Vac	1A	79.6mS	
230Vac	1A	65.6mS	





Vin:115Vac Io: 1A
Ch1: MOSFET's drain voltage, 100V/div
Ch2: output voltage, 5V/div



3.2 OUTPUT VOLTAGE RISE TIME

Input voltage	Output current	Startup time	Pass/Fail
115Vac	1A	21.6mS	
230Vac	1A	18.8mS	







Vin:230Vac Io: 1A
Ch1: MOSFET's drain voltage, 100V/div
Ch2: output voltage, 5V/div

3.3 OUTPUT VOLTAGE OVERSHOOT

Input voltage	Output current	overshoot voltage	Pass/Fail
115Vac	0A	<1%	
230Vac	0A	<1%	








3.4 RIPPLE VOLTAGE


Input voltage	Output current	Ripple voltage	Pass/Fail
115Vac	0.25A	39mV	
115Vac	0.5A	58mV	
115Vac	0.75A	52mV	
115Vac	1A	48mV	


230Vac	0.25A	38mV	
230Vac	0.5A	59mV	
230Vac	0.75A	49mV	
230Vac	1A	50mV	






















3.5 DYNAMIC RESPONSE

Input voltage	Output current	Max voltage	Min voltage
115Vac	0-0.5A	5.12V	4V
230Vac	0-0.5A	5.12V	4V






Vin:115Vac test condition: 0-0.5A, 0.1A/us, 10ms cycle, 1m USB cable

Ch1: output voltage, 500mV/div

Ch4: output current, 500mA/div


3.6 OUTPUT VOLTAGE PROTECTION


CONDITIONS	Protection voltage (V)	Pass/Fail
Vin (Vac)		
115&230	5.75	



3.7 OUTPUT SHORT PROTECTION


Input voltage	Output short protection
115&230Vac	Hiccup up mode






Vin:115Vac
Ch1: Vcc, 20V/div
Ch2: MOSFET's drain voltage, 100V/div
Ch3: output voltage, 5V/div
Ch4: output current, 10A/div


4 IV CURVE




5 THERMAL IMAGE




Component side, 115Vac and 1A load



Soldering side, 115Vac and 1A load





Component side, 230Vac and 1A load





Soldering side, 230Vac and 1A load

6 EMI Test









IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components which meet ISO/TS16949 requirements, mainly for automotive use. Components which have not been so designated are neither designed nor intended for automotive use; and TI will not be responsible for any failure of such components to meet such requirements.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com