





Contents

1	Photos.....	3
2	No Load Input Power	3
3	Efficiency	4
3.1	5V Flyback	4
3.2	3.3V Buck.....	5
3.3	2.5V Buck.....	6
3.4	1.5V Buck.....	7
3.5	1.0V Buck.....	8
4	Load Regulation	9
4.1	5V Flyback	9
4.2	3.3V Buck.....	9
4.3	2.5V Buck.....	10
4.4	1.5V Buck.....	10
4.5	1.0V Buck.....	11
5	5V Flyback Current Regulation.....	11
6	Thermal Images.....	12
6.1	5V Flyback	12
6.2	3.3V Buck.....	13
6.3	2.5V Buck.....	13
6.4	1.5V Buck.....	14
6.5	1.0V Buck.....	14
7	Startup	15
7.1	5V Flyback; 120VAC/60Hz – No Load	15
7.2	5V Flyback; 120VAC/60Hz – 1 Ω Load	15
7.3	3.3V Buck; 5V Input – No Load	16
7.4	3.3V Buck; 5V Input – 2 Ω Load	16
7.5	2.5V Buck; 5V Input – No Load	17
7.6	2.5V Buck; 5V Input – 2 Ω Load	17
7.7	1.5V Buck; 5V Input – No Load	18
7.8	1.5V Buck; 5V Input – 1 Ω Load	18
7.9	1.0V Buck; 5V Input – No Load	19
7.10	1.0V Buck; 5V Input – 1 Ω Load	19
8	Output Ripple Voltage	20
8.1	5V Flyback; 5A Load	20
8.2	3.3V Buck; 2A Load.....	20
8.3	3.3V Buck; 0A Load.....	21

8.4	2.5V Buck; 2A Load.....	21
8.5	2.5V Buck; 0A Load.....	22
8.6	1.5V Buck; 3A Load.....	22
8.7	1.5V Buck; 0A Load.....	23
8.8	1.0V Buck; 5A Load.....	23
8.9	1.0V Buck; 0A Load.....	24
9	5V Flyback Loop Response	24
10	Load Transients	25
10.1	5V Flyback	25
10.2	3.3V Buck.....	25
10.3	2.5V Buck.....	26
10.4	1.5V Buck.....	26
10.5	1.0V Buck.....	27
11	5V Flyback Switching Waveforms	27
11.1	Drain of Primary FET – Q2	27
11.2	Drain of Sync FET – Q1	28
12	Conducted Emissions	29

1 Photos

The photographs below show the PMP11180 Rev A prototype assembly.




2 No Load Input Power

Supply	Input Power	Test Setup
All Supplies Enabled	69mW	No modifications
5V Flyback Only	61mW	R23, R24, R31, and R35 removed
3.3V Buck Only	8mW	R1, R15, R24, R31, and R35 removed; U1-pin 6 lifted; External 5V input supply
2.5V Buck Only	7mW	R1, R15, R23, R24, and R35 removed; U1-pin 6 lifted; External 5V input supply
1.5V Buck Only	6mW	R1, R15, R23, R31, and R35 removed; U1-pin 6 lifted; External 5V input supply
1.0V Buck Only	8mW	R1, R15, R23, R24, and R31 removed; U1-pin 6 lifted; External 5V input supply

3 Efficiency

3.1 5V Flyback

All other supplies were disabled during this test.




120VAC/60Hz								
Iout	Vout	Vin	Iin	Pin	PF	Pout	Losses	Efficiency
0.000	4.98	120.1	0.0108	0.06112		0.00	0.061	
0.00100	4.98	120.1	0.0108	0.06767		0.00	0.063	7.4%
0.00996	4.98	120.1	0.0114	0.12655		0.05	0.077	39.2%
0.100	4.97	119.9	0.0224	0.673	0.251	0.50	0.18	73.8%
0.500	4.97	119.9	0.075	2.96	0.327	2.49	0.48	84.0%
1.250	4.97	119.9	0.150	7.25	0.403	6.21	1.04	85.7%
1.875	4.97	119.9	0.205	10.88	0.442	9.32	1.56	85.7%
2.500	4.97	119.9	0.257	14.53	0.471	12.43	2.11	85.5%
3.125	4.97	119.9	0.307	18.16	0.494	15.53	2.63	85.5%
3.750	4.97	119.9	0.355	21.80	0.513	18.64	3.16	85.5%
4.375	4.97	119.9	0.402	25.45	0.528	21.74	3.71	85.4%
4.989	4.97	119.9	0.449	29.05	0.540	24.80	4.25	85.4%

Vin	Pin	Vout	Iout	Load	Efficiency	Avg. Eff.
120VAC/60Hz	2.96	4.97	0.500	10%	83.95%	
	7.25	4.97	1.250	25%	85.69%	85.51%
	14.53	4.97	2.500	50%	85.51%	
	21.80	4.97	3.750	75%	85.49%	
	29.05	4.97	4.989	100%	85.35%	

3.2 3.3V Buck


All other supplies were disabled during this test.



Iout	Vout	Vin	Iin	Pin	Pout	Losses	Efficiency
0.000	3.315	4.98	0.00160	0.008	0.00	0.008	
0.00100	3.314	4.98	0.00230	0.011	0.00	0.008	28.9%
0.00999	3.313	4.97	0.00889	0.044	0.03	0.011	74.9%
0.099	3.310	5.00	0.073	0.365	0.33	0.037	89.8%
0.500	3.305	5.02	0.350	1.757	1.65	0.10	94.1%
0.750	3.296	4.99	0.529	2.640	2.47	0.17	93.6%
1.000	3.288	4.99	0.711	3.548	3.29	0.26	92.7%
1.250	3.281	4.99	0.899	4.486	4.10	0.38	91.4%
1.500	3.272	4.99	1.094	5.459	4.91	0.55	89.9%
1.750	3.266	4.99	1.305	6.512	5.72	0.80	87.8%
2.000	3.255	5.01	1.519	7.610	6.51	1.10	85.5%

3.3 2.5V Buck


All other supplies were disabled during this test.



Iout	Vout	Vin	Iin	Pin	Pout	Losses	Efficiency
0.000	2.497	5.01	0.00142	0.007	0.00	0.007	
0.00100	2.497	5.01	0.00196	0.010	0.00	0.007	25.4%
0.01002	2.497	5.00	0.00693	0.035	0.03	0.010	72.2%
0.100	2.495	5.01	0.057	0.286	0.25	0.036	87.4%
0.499	2.504	4.97	0.273	1.357	1.25	0.11	92.1%
0.750	2.503	4.98	0.412	2.052	1.88	0.17	91.5%
1.000	2.495	4.98	0.554	2.759	2.50	0.26	90.4%
1.250	2.493	5.02	0.696	3.494	3.12	0.38	89.2%
1.500	2.489	5.00	0.854	4.270	3.73	0.54	87.4%
1.750	2.497	4.97	1.023	5.084	4.37	0.71	85.9%
2.000	2.494	5.00	1.192	5.960	4.99	0.97	83.7%

3.4 1.5V Buck


All other supplies were disabled during this test.



I _{out}	V _{out}	V _{in}	I _{in}	P _{in}	P _{out}	Losses	Efficiency
0.000	1.505	4.98	0.00115	0.006	0.00	0.006	
0.00101	1.505	4.98	0.00148	0.007	0.00	0.006	20.6%
0.01004	1.505	4.98	0.00454	0.023	0.02	0.007	66.8%
0.100	1.503	5.01	0.036	0.180	0.15	0.030	83.3%
0.750	1.486	5.01	0.250	1.253	1.11	0.14	89.0%
1.125	1.483	5.01	0.377	1.889	1.67	0.22	88.3%
1.500	1.481	4.99	0.510	2.545	2.22	0.32	87.3%
1.875	1.478	5.00	0.648	3.240	2.77	0.47	85.5%
2.250	1.476	5.01	0.793	3.973	3.32	0.65	83.6%
2.625	1.479	5.01	0.949	4.754	3.88	0.87	81.7%
3.000	1.476	5.01	1.116	5.591	4.43	1.16	79.2%

3.5 1.0V Buck


All other supplies were disabled during this test.




I _{out}	V _{out}	V _{in}	I _{in}	P _{in}	P _{out}	Losses	Efficiency
0.000	1.019	4.98	0.00154	0.008	0.00	0.008	
0.00102	1.016	4.98	0.00147	0.007	0.00	0.006	14.2%
0.01013	1.016	4.98	0.00367	0.018	0.01	0.008	56.3%
0.101	1.019	5.01	0.026	0.130	0.10	0.027	79.0%
0.502	1.013	5.00	0.120	0.600	0.51	0.09	84.8%
1.248	1.011	5.00	0.299	1.495	1.26	0.23	84.4%
1.877	1.010	5.00	0.465	2.325	1.90	0.43	81.5%
2.496	1.010	5.00	0.645	3.225	2.52	0.70	78.2%
3.125	1.009	5.00	0.847	4.235	3.15	1.08	74.5%
3.748	1.010	4.99	1.077	5.374	3.79	1.59	70.4%
4.373	1.010	5.01	1.350	6.764	4.42	2.35	65.3%
5.001	1.013	5.01	1.690	8.467	5.07	3.40	59.8%

4 Load Regulation


4.1 5V Flyback




4.2 3.3V Buck




4.3 2.5V Buck




4.4 1.5V Buck



4.5 1.0V Buck





5 5V Flyback Current Regulation



6 Thermal Images


6.1 5V Flyback

All other supplies were disabled during this test. The 5V output was loaded with 5A. The ambient temperature was 25°C with no forced air flow. The input was 120VAC/60Hz.




6.2 3.3V Buck

All other supplies were disabled during this test. The 3.3V output was loaded with 2A. The ambient temperature was 25°C with no forced air flow. The input was 5VDC.




6.3 2.5V Buck

All other supplies were disabled during this test. The 2.5V output was loaded with 2A. The ambient temperature was 25°C with no forced air flow. The input was 5VDC.




6.4 1.5V Buck

All other supplies were disabled during this test. The 1.5V output was loaded with 3A. The ambient temperature was 25°C with no forced air flow. The input was 5VDC.




6.5 1.0V Buck

All other supplies were disabled during this test. The 1.0V output was loaded with 3.8A. The ambient temperature was 25°C with no forced air flow. The input was 5VDC.






7 Startup



7.1 5V Flyback; 120VAC/60Hz – No Load







7.2 5V Flyback; 120VAC/60Hz – 1Ω Load



7.3 3.3V Buck; 5V Input – No Load**7.4 3.3V Buck; 5V Input – 2Ω Load**


7.5 2.5V Buck; 5V Input – No Load**7.6 2.5V Buck; 5V Input – 2Ω Load**

7.7 1.5V Buck; 5V Input – No Load**7.8 1.5V Buck; 5V Input – 1Ω Load**


7.9 1.0V Buck; 5V Input – No Load**7.10 1.0V Buck; 5V Input – 1Ω Load**



8 Output Ripple Voltage



8.1 5V Flyback; 5A Load





8.2 3.3V Buck; 2A Load




8.3 3.3V Buck; 0A Load**8.4 2.5V Buck; 2A Load**

8.5 2.5V Buck; 0A Load**8.6 1.5V Buck; 3A Load**


8.7 1.5V Buck; 0A Load**8.8 1.0V Buck; 5A Load**

8.9 1.0V Buck; 0A Load




9 5V Flyback Loop Response

Output was loaded with 5A. The input was 120VAC/60Hz.






10 Load Transients

10.1 5V Flyback




10.2 3.3V Buck



10.3 2.5V Buck**10.4 1.5V Buck**


10.5 1.0V Buck




11 5V Flyback Switching Waveforms

The input was 132VAC/60Hz, and the output was loaded with 5A.


11.1 Drain of Primary FET – Q2



11.2 Drain of Sync FET – Q1

12 Conducted Emissions

The 5V flyback was loaded with a 5A resistive load. All buck regulators were unloaded.



IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.